

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Oversized Hot Dip Galvanised, Class 8.8 M16X50

Article number	01430.160.050
Brand	-
UBB	950351211020
UNSPSC	31161620
EAN	8715492412485
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

ASME	B18.2.3.1M
NF	E25-114
ISO	4017
DIN	933
NEN	1568

Technical Specification

d-D	M16
k	10
L (mm)	50
P	2
s	24

Technical Drawing

