



## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M24X120

Article number	01400.240.120
Brand	-
UBB	950351196841
UNSPSC	31161620
EAN	8715492409423
PKG. of 10	Full Box Only

### Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	120
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

### Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

### Technical Specification

b (min.):	60
125mm<L≤200mm	

### Technical Drawing

b (min.):  $L > 200\text{mm}$  73

b (min.):  $L \leq 125\text{mm}$  54

**ur course**  
k SETTING THE STANDARD  
IN FASTENING SOLUTIONS 15

P 3

s 36

