

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M6X30

|                |               |
|----------------|---------------|
| Article number | 04105.060.030 |
| Brand          | -             |
| UBB            | 500505619899  |
| UNSPSC         | 31161620      |
| EAN            | 8715494438865 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                   |                                                                     |
|-------------------|---------------------------------------------------------------------|
| Diameter          | M6                                                                  |
| Length            | 30 mm                                                               |
| Class             | 10.9                                                                |
| Driving features  | Hexagon                                                             |
| Head shape        | Hexagon head                                                        |
| Material          | Steel                                                               |
| Thread direction  | Right                                                               |
| Surface treatment | Zinc flake Cr6+free - ISO 10683 flZnnc                              |
| Thread            | Metric thread                                                       |
| Info              | A zinc flake coating eliminates the risk of hydrogen embrittlement. |

### Standards

|      |            |
|------|------------|
| ASME | B18.2.3.1M |
| DIN  | 931        |
| NF   | E25-112    |
| ISO  | 4014       |
| NEN  | 1555       |

### Technical Specification

|                           |    |
|---------------------------|----|
| b (min.):<br>125mmL≤200mm | 24 |
| b (min.): L≤125mm         | 18 |
| d-D                       | M6 |
| k                         | 4  |
| L (mm)                    | 30 |
| P                         | 1  |
| s                         | 10 |

### Technical Drawing

