

ISO 4014 Partially Threaded Metric Hexagon Head Bolt, Steel (AD-W7), Plain, Class 5.6 M24X120

Article number	08750.240.120
Brand	-
UBB	950351671215
UNSPSC	31161620
EAN	8715492564061
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	5.6
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel (AD-W7)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Technical Specification

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L > 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	120
P	3
s	36

Technical Drawing

