

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised - Oversized, Class 8.8 M24X75

Article number	01420.240.075
Brand	-
UBB	950351207994
UNSPSC	31161620
EAN	8715492411792
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

ISO	4014
DIN	931
NEN	1555
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	75
P	3
s	36

Technical Drawing

