

ISO 4017 Fully Threaded Metric Hexagon Head Bolt, Steel (AD-W7), Plain, Class 5.6 M16X50

Article number	08760.160.050
Brand	-
UBB	950351673526
UNSPSC	31161620
EAN	8715492564474
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	50 mm
Class	5.6
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel (AD-W7)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standards

NF	E25-114
DIN	933
ISO	4017
NEN	1568
ASME	B18.2.3.1M

FABORY

certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Technical Specification

d-D	M16
k	10
L (mm)	50
P	2
s	24

Technical Drawing

