FABORY



Disc spring for critical applications Steel Ck 67 Werkstoffnr. 1.1231 Phosphated 15X6,2X0,7MM

Article number	36450.156.007
Brand	-
UBB	950357493408
UNSPSC	31161811
EAN	8715492761910
PKG. of 100	Full Box Only

Technical Parameters

Diameter	6.2 mm
d_e	15
di	6.2
Material	Steel
Material technical	Ck 67 Werkstoffnr. 1.1231
Outer diameter	15
Surface treatment	Phosphated
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Disc springs are mostly used in critical applications with safety first. Similar applications can be found in for example safety torque limiter clutches, hinge stiffeners and applications of constant roll pressure. Because of the right combination c.q. stacking of the disc

Standards

FABORY

springs the elasticity and/or deflection can be dosed accurately. The technical specifications of these disc springs meet the highest expectations with reference to the static and dynamic load. They exceed the requirements of DIN 2093.Material group 1: t 1,25 from steel Ck 67.Material group 2: 1,25 ≤ t ≤ 6,0 from steel 50 Cr V4.Material group 3: 6,0 t ≤ 14,0 from steel 50 Cr V4.Fatique fractures can be largely prevented because the disc springs of material group 2 and 3 have machined edges.F = spring force in Newton at a deflection s ≈ 0,75 ho(ho= Lo– t).For the calculation of disc springs, see DIN 2092.Extensive technical data available on request.

Technical Specification

di (H12)	6.2
D (mm)	6.2
F	578
l0	1.1
t	0.7
Thickness	0.7

Technical Drawing

