



**Hexagon socket  
countersunk head screw  
ISO 10642 Steel Zinc flake  
Cr6+free - ISO 10683 flZnnc  
010.9 M20X50**

Article number	07407.200.050
Brand	-
UBB	500571183127
UNSPSC	31161518
EAN	8715494137812
PKG. of 10	Full Box Only

**Technical Parameters**

Diameter	M20
Length	50 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info

A zinc flake coating eliminates the risk of hydrogen embrittlement. All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a

**Standards**

ISO	10642
DIN	≈7991

'0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Technical Specification

b (min.)	60
d-D	M20
dk (max.)	36.75
Full thread if $L \leq$	90
k (max.)	10.16
L (mm)	50
P	2.5
s	12
$\alpha$	90

## Technical Drawing

