



## Hexagon socket set screw with cone point DIN 914 Stainless steel A2 M10X25

|                |               |
|----------------|---------------|
| Article number | 51250.100.025 |
| Brand          | -             |
| UBB            | 952351521960  |
| UNSPSC         | 31161518      |
| EAN            | 8715492277657 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |                                                                                                    |
|--------------------|----------------------------------------------------------------------------------------------------|
| Diameter           | M10                                                                                                |
| Length             | 25 mm                                                                                              |
| Driving features   | Hexagon socket                                                                                     |
| Material           | Stainless steel                                                                                    |
| Material technical | A2                                                                                                 |
| Thread direction   | Right                                                                                              |
| Point              | Cone                                                                                               |
| Thread             | Metric thread                                                                                      |
| Info               | These set screws are designed for pressure loads and are not suitable for tensile- or shear loads. |

### Standards

|      |          |
|------|----------|
| BS   | 4168-3   |
| ISO  | 4027     |
| NEN  | 2342     |
| ASME | B18.3.6M |
| NF   | E27-181  |
| DIN  | 914      |

### Technical Specification

|           |     |
|-----------|-----|
| d-D       | M10 |
| dt (max.) | 2.5 |
| L (mm)    | 25  |
| P         | 1.5 |
| s         | 5   |
| t (min.)  | 4   |

### Technical Drawing

