



Machine screw flat countersunk slot UNC asme B18.6.3 ASME B18.6.3 Brass #12-24X3/4

Article number	U48170.021.0075
Brand	-
UBB	500624967781
UNSPSC	31161504
EAN	8715492982292
PKG. of 50	Full Box Only

Technical Parameters

Diameter	NO.12
Length	3/4 Inch
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	24
Info	Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.412
H (max.)	0.132
J (max.)	0.067

Technical Drawing

T (max.) 0.06
FABORY

