



## Machine screw flat countersunk slot UNC asme B18.6.3 ASME B18.6.3 Brass 3/8-16X1.1/2

Article number	U48170.037.0150
Brand	-
UBB	500624969761
UNSPSC	31161504
EAN	8717077790087
PKG. of 10	Full Box Only

### Technical Parameters

Diameter	3/8 Inch
Length	1.1/2 Inch
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	16
Info	Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME	B18.6.3
------	---------

### Technical Specification

A (max.)	0.717
H (max.)	0.23
J (max.)	0.094

### Technical Drawing

T (max.) 0.106

**FABORY**

