



Disc spring for critical applications Steel 50 Cr V4 Werkstoffnr. 1.8159 Phosphated 70X40,5X5,0MM

Article No.	36450.740.050
Brand	-
UBB	950357385257
UNSPSC	31161811
EAN	8715492762726
PKG. of 5	Full Box Only

Technical Parameters

De	70
Di	40.5
Diameter (mm)	40.5
t	5
Material	Steel
Material technical	50 Cr V4 Werkstoffnr. 1.8159
Outer diameter	70
Surface treatment	Phosphated
Thickness	5.0 mm

Info

Disc springs are mostly used in critical applications with safety first. Similar applications can be found in for example safety torque limiter clutches, hinge stiffeners and applications of constant roll pressure. Because of the right combination c.q. stacking of the disc springs the elasticity

Standards

and/or deflection can be dosed accurately.

The technical specifications of these disc springs meet the highest expectations with reference to the static and dynamic load. They exceed the requirements of DIN 2093. Material group 1: $t < 1,25$ from steel Ck 67. Material group 2: $1,25 \leq t \leq 6,0$ from steel 50 Cr V4. Material group 3: $6,0 < t \leq 14,0$ from steel 50 Cr V4. Fatigue fractures can be largely prevented because the disc springs of material group 2 and 3 have machined edges. F = spring force in Newton at a deflection $s \approx 0,75 h_0$ ($h_0 = L_0 - t$). For the calculation of disc springs, see DIN 2092. Extensive technical data available on request.

Info Warning: electroplating of these products may cause hydrogen embrittlement.

Technical Specification

D_i (H12)	40.5
F	33672
l_0	6.2
t	5

Technical Drawing

