

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A2-70 M10X55

|                |               |
|----------------|---------------|
| Article number | 51000.100.055 |
| Brand          | -             |
| UBB            | 950351764374  |
| UNSPSC         | 31161620      |
| EAN            | 8715492250650 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |                                                                                      |
|--------------------|--------------------------------------------------------------------------------------|
| Diameter           | M10                                                                                  |
| Length             | 55 mm                                                                                |
| Class              | 70                                                                                   |
| Driving features   | Hexagon                                                                              |
| Head shape         | Hexagon head                                                                         |
| Material           | Stainless steel                                                                      |
| Material technical | A2                                                                                   |
| Thread direction   | Right                                                                                |
| Thread             | Metric thread                                                                        |
| Info               | Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. |

### Standards

|      |            |
|------|------------|
| ASME | B18.2.3.1M |
| NF   | E25-112    |
| ISO  | 4014       |
| DIN  | 931        |
| NEN  | 1555       |

### Technical Specification

|                           |     |
|---------------------------|-----|
| b (min.):<br>125mmL≤200mm | 32  |
| b (min.): L200mm          | 45  |
| b (min.): L≤125mm         | 26  |
| d-D                       | M10 |
| k                         | 6.4 |
| L (mm)                    | 55  |
| P                         | 1.5 |

### Technical Drawing



