

## Espárrago dos roscas $\approx 1d$ DIN 938 Acero Cincado 5.6 (AD-W7) para equipos de presión M16X45



Artículo No.	21546.160.045
Marca	-
UBB	500648212214
UNSPSC	31161610
EAN	8717077220164
Env. de 50	Solo embalaje completo

### Parámetros técnicos

Diámetro (d-D)	M16
Anchura (L) (mm)	45
Clase	5.6 (AD-W7)
Material (largo)	Acero
Tratamiento de superficie	Cincado
Dirección del hilo	Derecha
Rosca (larga)	Métrica

Información adicional para equipos de presión

Observaciones  
ATTENTION: when ordering studs according to this DIN standard the proper designation is d x L, e.g. stud M10X70 - DIN 938, where the working length L = 70 mm and the thread length on the metal end  $b_m = 10$  mm. The overall length of the stud is  $70 + 10 = 80$  mm. The thread length on the nut end  $b = 26$  mm. The thread

### Normas

DIN	938
NF	E25-135

tolerance class on the metal end is Sk6 according to DIN 13-51, meaning "transition fit", which prevents loosening of the metal end of the studs during disassembly. In case this transition fit is not wanted, add "Fo" in the designation. These studs have thread tolerance class 6g on both ends and can be supplied as specials. Studs according to DIN 938 with a metal end  $\approx 1d$  have many applications, but are mainly intended for use in steel counterparts.

### Especificación técnica

b	38
$b_m \approx 1d$	16
$b = L - (x+3)$ up to $L \leq$	45
P	2
x	5

### Diseño técnico

