



## Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) 1/4-20X1.1/4

Article number	U51122.025.0125
Brand	-
UBB	500625009427
UNSPSC	31161504
EAN	8717077794313
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	1/4 Inch
Length	1.1/4 Inch
Driving features	Phillips
Head shape	Pan head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	20

Info

Screws with diameter  $\leq$  No.5 and length  $\leq$  1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length  $\leq$  2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME B18.6.3

### Technical Specification

A (max.)	0.492
H (max.)	0.175

### Technical Drawing

**FABORY**

