



M10

Artículo No.	90247FIS
Marca	-
UBB	500616785175
UNSPSC	31161607
EAN	4006209902479
Env. de 1	Solo embalaje completo

Parámetros técnicos

Diámetro	M10
Características clave	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TA M can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l s : $\text{Screw length } l s = \text{Length of fixing} + \text{Thickness of fixture} + \text{Thickness of washer}.$
Aprobación de ETA	Yes

Info

do= Nominal diameter of drill bit.
 dd= Embedment depth.
 df= Anchor diameter.
 fs= Head diameter.
 Ws=

Normas

FABORY

Setting tool
diameter.hef=
Effective anchorage
depth.tfix= Grip
range.kN =
Allowable load in kN.

Especificación técnica

Diseño técnico

