



Boulon avec écrou pour les appareils à pression ISO 4014/4032 Acier Galvanisé à chaud 5.6/5.2 M16X110

Numéro d'article 08753.160.110

Marque -

UBB 500650921942

UNSPSC 31161620

EAN 8717077306660

PKG. de 25 Boîte complete uniquement

Paramètres techniques

Diamètre	M16
Longueur	110 mm
Classe	5.6/5.2
Mode d'entraînement	Hexagonale
Forme de tête	Tête hexagonale
Matière	Acier
Direction du filetage	Droit
Revêtement	Galvanisé à chaud
Filetage	Filetage métrique

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are

Normes

ISO 4014/4032

FABORY

entitled to replace a
certificate EN 10204
3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy.

Spécifications techniques

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	110
m (max.)	14.8
P	2
s	24

Dessin technique

