

Goujon longueur d'implantation $\approx 2d$ DIN 835 Acier inoxydable (Inox) A2 M16X35



Numéro d'article	51285.160.035
------------------	---------------

Marque	-
--------	---

UBB	500696050177
-----	--------------

UNSPSC	31163300
--------	----------

EAN	8715492035011
-----	---------------

PKG. de 50	Boîte complete uniquement
------------	---------------------------

Paramètres techniques

Diamètre	M16
----------	-----

Longueur	35 mm
----------	-------

Matière	Acier inoxydable
---------	------------------

Matière technique	A2
-------------------	----

Direction du filetage	Droit
-----------------------	-------

Filetage	Filetage métrique
----------	-------------------

Info	<p>ATTENTION: when ordering studs according to this DIN standard the proper designation is d x L, e.g. stud M10X70 - DIN 835, where the working length $L = 70$ mm and the thread length on the metal end $b_m = 20$ mm. The overall length of the stud is $70 + 20 = 90$ mm. The thread length on the nut end $b = 26$ mm. The thread tolerance class on the metal end is Sk6 according to DIN 13-51, meaning "transition fit", which</p>
------	--

Normes

DIN	835
-----	-----

prevents loosening of the metal end of the studs during disassembly. In case this transition fit is not wanted, add "Fo" in the designation. These studs have thread tolerance class 6g on both ends and can be supplied as specials. Studs according to DIN 835 with a metal end $\approx 2d$ have many applications, but are mainly intended for use in aluminium alloy counterparts.

Spécifications techniques

b: $L \leq 125\text{mm}$	38
b: $125\text{mm} < L \leq 200\text{mm}$	44
b: $L \geq 200\text{mm}$	57
b_m	32
$b_2 = L - (x_1 + 3)$ à $L \leq$	45
d-D	M16
L (mm)	35
P	2
x	5

Dessin technique

