



M10

Numéro d'article	90247FIS
Marque	-
UBB	500616785175
UNSPSC	31161607
EAN	4006209902479
PKG. de 1	Boîte complete uniquement

Paramètres techniques

Diamètre	M10
Principales caractéristiques	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TA M can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l s : Screw length l s = Length of fixing + Thickness of fixture t fix + Thickness of washer.
ETA-approval	Yes

Info

do= Nominal diameter of drill bit.
dd= Embedment depth.
df= Anchor diameter.
fs= Head diameter.
Ws=

Normes

FABORY

Setting tool
diameter.hef=
Effective anchorage
depth.tfix= Grip
range.kN =
Allowable load in kN.

Spécifications techniques

Dessin technique

