



## Cheville haute performance type FH II-B M16X160/30

Numéro d'article	97035FIS
Marque	-
UBB	500616707468
UNSPSC	31162101
EAN	4006209970355
PKG. de 10	Boîte complete uniquement

### Paramètres techniques

Diamètre	M16
Info	<p>do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor <math>\gamma_f = 1,4</math> and if the <math>S_{cr}</math>, N and <math>C_{cr}</math>, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should</p>

### Normes

# FABORY

comply with the  
complete European  
Technical Approval  
(ETA), this approval  
is also available on  
request.

## Spécifications techniques

## Dessin technique

