



Cheville haute performance type FH II-B M16X95/165

Numéro d'article	97644FIS
Marque	-
UBB	500616712310
UNSPSC	31162101
EAN	4006209976449
PKG. de 10	Boîte complete uniquement

Paramètres techniques

Diamètre	M16
Info	do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr}, N and C_{cr}, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should

Normes

FABORY comply with the complete European Technical Approval (ETA), this approval is also available on request.

Spécifications techniques

Dessin technique

