



Écrou hexagonal bas MF DIN 439 2 Acier inoxydable (Inox) A2 Min.50 M14X1,50

Numéro d'article	51092.140.150
Marque	-
UBB	950355569357
UNSPSC	31161727
EAN	8715492268204
PKG. de 50	Boîte complete uniquement

Paramètres techniques

Diamètre	M14
Classe	Min.50
Mode d'entraînement	Hexagonale
Matière	Acier inoxydable
Matière technique	A2
Direction du filetage	Droit
Filetage	Metric fine thread

Info

do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.When

Normes

DIN	439-2
NEN	2334-B
ASME	B18.2.4.5M
ISO	8675
NF	E25-453

reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Spécifications techniques

d-D	M14
m	7
P	1.5
s	22

Dessin technique

