



## Assembly set for pressure vessels, fully threaded ISO 4017/4032 Steel (AD-W7) Hot dip galvanized 5.6/5.2 for pressure vessels M16X60

Numero articolo	08762.160.060
Marchio	-
UBB	500648359577
UNSPSC	31161620
EAN	8717077245877
PKG. di 50	Solo full box

### Parametri tecnici:

Diametro	M16
Lunghezza	60 mm
Class	5.6/5.2
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel (AD-W7)
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

### Standard

ISO	4017/4032
-----	-----------

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-

Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy for pressure vessels

## Specifica tecnica

d-D	M16
k	10
L (mm)	60
m (max.)	14.8
P	2
s	24

## Disegno tecnico

