

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

1 Identification of the substance/mixture and of the company/undertaking

- **Product identifier**
- **Trade name:** MOTIP SPRAY PUTTY
- **Article number:** 04062
- **Relevant identified uses of the substance or mixture and uses advised against**
- **Application of the substance / the preparation** Paint
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL-8471 XC Wolvega
The Netherlands
Tel: +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail info@nl.motipdupli.com
- **Further information obtainable from:** QHSE Department
- **Emergency telephone number:** Tel: +31 (0)561 694400 (08.00 / 17.00)

2 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Aerosol 1 H222 Extremely flammable aerosol.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2 H319 Causes serious eye irritation.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xn; Harmful

R20/21: Harmful by inhalation and in contact with skin.



Xi; Irritant

R38: Irritating to skin.



F+; Extremely flammable

R12: Extremely flammable.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

- **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

Warning! Pressurized container.

- **Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 1)

· **Label elements**

· **Labelling according to EU guidelines:**

The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

· **Code letter and hazard designation of product:**



Xn Harmful
F+ Extremely flammable

· **Hazard-determining components of labelling:**

xylene

· **Risk phrases:**

- 12 Extremely flammable.
20/21 Harmful by inhalation and in contact with skin.
38 Irritating to skin.
52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

· **Safety phrases:**

- 2 Keep out of the reach of children.
16 Keep away from sources of ignition - No smoking.
23 Do not breathe aerosol.
29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.
36/37 Wear suitable protective clothing and gloves.
46 If swallowed, seek medical advice immediately and show this container or label.
51 Use only in well-ventilated areas.

· **Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
Do not spray on a naked flame or any incandescent material.

· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
· **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 1330-20-7 EINECS: 215-535-7	xylene Xn R20/21 Xi R38 R10 <hr/> Flam. Liq. 3, H226 Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	20-25%
CAS: 74-98-6 EINECS: 200-827-9	propane F+ R12 <hr/> Flam. Gas 1, H220 Press. Gas, H280	12.5-20%

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31



























Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 2)

CAS: 106-97-8 EINECS: 203-448-7	butane  F+ R12  Flam. Gas 1, H220  Press. Gas, H280	10-12.5%
CAS: 75-28-5 EINECS: 200-857-2	isobutane  F+ R12  Flam. Gas 1, H220  Press. Gas, H280	5-10%
CAS: 64742-49-0 EINECS: 265-151-9	Naphtha (petroleum), hydrotreated light  Xn R65  Xi R38  F R11  N R51/53 R67  Asp. Tox. 1, H304	5-10%
CAS: 67-64-1 EINECS: 200-662-2	acetone  Xi R36  F R11 R66-67  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	5-10%
CAS: 71-36-3 EINECS: 200-751-6	butan-1-ol  Xn R22  Xi R37/38-41 R10-67  Flam. Liq. 3, H226  Eye Dam. 1, H318  Acute Tox. 4, H302; STOT SE 3, H335+H336 Skin Irrit. 2, H315	1-2.5%
CAS: 58052-10-1	Blister free 45  Xi R37-41  N R51/53 R10-67  Flam. Liq. 3, H226  Eye Dam. 1, H318  Aquatic Chronic 2, H411  STOT SE 3, H335+H336	0.1-1%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

4 First aid measures

· **Description of first aid measures**

· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:**

Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.

In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Heating may cause a fire or explosion.

· **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.

· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 3)

- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Firefighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
Keep away from ignition sources.
- **Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **Handling:**
- **Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
- **Information about fire - and explosion protection:**
Do not spray onto a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Store in a cool location.
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
Keep container tightly sealed.
Protect from heat and direct sunlight.
- **Specific end use(s)** No further relevant information available.

GB

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: **MOTIP SPRAY PUTTY**

(Contd. of page 4)

8 Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

1330-20-7 xylene

WEL Short-term value: 441 mg/m³, 100 ppm
Long-term value: 220 mg/m³, 50 ppm
Sk; BMGV

106-97-8 butane

WEL Short-term value: 1810 mg/m³, 750 ppm
Long-term value: 1450 mg/m³, 600 ppm
Carc (if more than 0.1% of buta-1,3-diene)

67-64-1 acetone

WEL Short-term value: 3620 mg/m³, 1500 ppm
Long-term value: 1210 mg/m³, 500 ppm

71-36-3 butan-1-ol

WEL Short-term value: 154 mg/m³, 50 ppm
Sk

· **Additional information:** The lists valid during the making were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the skin.

Avoid contact with the eyes and skin.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Not required.

GB

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 5)

9 Physical and chemical properties

· Information on basic physical and chemical properties	
· General Information	
· Appearance:	
Form:	Aerosol
Colour:	According to product specification
· Odour:	Characteristic
· Odour threshold:	Not determined.
· pH-value:	Not determined.
· Change in condition	
Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Not applicable, as aerosol.
· Flash point:	< 0°C (< 32°F) Not applicable, as aerosol.
· Ignition temperature:	365°C (689°F)
· Decomposition temperature:	Not determined.
· Self-igniting:	Product is not selfigniting.
· Danger of explosion:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	1.1 Vol %
Upper:	10.9 Vol %
· Vapour pressure at 20°C (68°F):	3500 hPa (2625 mm Hg)
· Density at 20°C (68°F):	0.795 g/cm ³ (6.634 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Segregation coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	74.9 %
· EU-VOC:	595.4 g/l
· EU-VOC in %:	74.89 %
· Solids content:	24.6 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 6)

· **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

· **Information on toxicological effects**· **Acute toxicity:**· **LD/LC50 values relevant for classification:**

1330-20-7 xylene

Oral	LD50	4300 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
	LC50 / 4 h	22.1 mg/m3 (rat)

106-97-8 butane

	LC50 / 4 h	658 mg/m3 (rat)
--	------------	-----------------

64742-49-0 Naphtha (petroleum), hydrotreated light

Oral	LD50	>5000 mg/kg (rat)
Dermal	LD50	>2600 mg/kg (rabbit)
	LC50 / 4 h	>193 mg/m3 (rat)

67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
Dermal	LD50	20000 mg/kg (rabbit)
	LC50 / 4 h	39 mg/m3 (rat)

71-36-3 butan-1-ol

Oral	LD50	4400 mg/kg (rat)
Dermal	LD50	4200 mg/kg (rabbit)
	LC50 / 4 h	25 mg/m3 (rat)

· **Primary irritant effect:**· **on the skin:** Irritant to skin and mucous membranes.· **on the eye:** No irritating effect.· **Sensitization:** No sensitizing effects known.· **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:

Harmful

Irritant

12 Ecological information

· **Toxicity**· **Aquatic toxicity:**

1330-20-7 xylene

EC50 / 48 h	7.4 mg/l (daphnia magna)
LC50 / 96 h	13.5 mg/l (fish)

64742-49-0 Naphtha (petroleum), hydrotreated light

LC50	127-159 mg/l (Leuciscus idus)
------	-------------------------------

67-64-1 acetone

EC50 / 48 h	39 mg/l (daphnia magna)
LC50 / 48 h	2262 mg/l (daphnia magna)
LC50 / 96 h (static)	5540 mg/l (fish)

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 7)

71-36-3 butan-1-ol

EC50 / 48 h	1983 mg/l (daphnia magna)
EC50 / 72 h	8500 mg/l (algae)

- **Persistence and degradability** No further relevant information available.
- **Behaviour in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
Harmful to aquatic organisms
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

* **13 Disposal considerations**

- **Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· European waste catalogue	
08 01 11*	waste paint and varnish containing organic solvents or other dangerous substances
15 01 04	metallic packaging

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

* **14 Transport information**

- **Land transport ADR/RID (cross-border)**



- **ADR/RID class:** 2 5F Gases.
- **Danger code (Kemler):** -
- **UN-Number:** 1950
- **Packaging group:** -
- **Hazard label** 2.1
- **UN proper shipping name:** 1950 AEROSOLS
- **Limited quantities (LQ)** LQ2
- **Transport category** 2
- **Tunnel restriction code** D

(Contd. on page 9)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 8)

· Maritime transport IMDG:

- **IMDG Class:** 2.1
- **UN Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **EMS Number:** F-D,S-U
- **Marine pollutant:** No
- **Proper shipping name:** AEROSOLS

· Air transport ICAO-TI and IATA-DGR:

- **ICAO/IATA Class:** 2.1
- **UN/ID Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **Proper shipping name:** AEROSOLS, flammable

- **UN "Model Regulation":** UN1950, AEROSOLS, 2.1
- **Special precautions for user** Warning: Gases.
- **Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code** Not applicable.

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Labelling according to EU guidelines:**
The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.
- **Code letter and hazard designation of product:**



Xn Harmful
F+ Extremely flammable

- **Hazard-determining components of labelling:**
xylene
- **Risk phrases:**
 - 12 Extremely flammable.
 - 20/21 Harmful by inhalation and in contact with skin.
 - 38 Irritating to skin.
 - 52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- **Safety phrases:**
 - 2 Keep out of the reach of children.
 - 16 Keep away from sources of ignition - No smoking.
 - 23 Do not breathe aerosol.
 - 29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.
 - 36/37 Wear suitable protective clothing and gloves.
 - 46 If swallowed, seek medical advice immediately and show this container or label.

(Contd. on page 10)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 34

Revision: 23.03.2011

Trade name: MOTIP SPRAY PUTTY

(Contd. of page 9)

51 Use only in well-ventilated areas.

· **Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H302 Harmful if swallowed.

H304 May be fatal if swallowed and enters airways.

H312 Harmful in contact with skin.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H335 May cause respiratory irritation.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.

R10 Flammable.

R11 Highly flammable.

R12 Extremely flammable.

R20/21 Harmful by inhalation and in contact with skin.

R22 Harmful if swallowed.

R36 Irritating to eyes.

R37 Irritating to respiratory system.

R37/38 Irritating to respiratory system and skin.

R38 Irritating to skin.

R41 Risk of serious damage to eyes.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

· **Department issuing MSDS:** QHSE Department

· **Contact:**

Mrs. D. Kleistra

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

· *** Data compared to the previous version altered.**