



Stud metal end $\approx 1d$ DIN 938 Stainless steel A2 M12X70

Numero articolo 51280.120.070

Marchio -

UBB 950353388214

UNSPSC 31161610

EAN 8715492279835

PKG. di 100 Solo full box

Parametri tecnici:

Diametro	M12
Lunghezza	70 mm
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standard

DIN	938
NF	E25-135

Info	<p>ATTENTION: when ordering studs according to this DIN standard the proper designation is d x L, e.g. stud M10X70 - DIN 938, where the working length $L = 70$ mm and the thread length on the metal end $b_m = 10$ mm. The overall length of the stud is $70 + 10 = 80$ mm. The thread length on the nut end $b = 26$ mm. The thread tolerance class on the metal end is Sk6 according to DIN 13-51, meaning "transition fit", which prevents loosening of the metal end of the studs during disassembly. In</p>
------	--

case this transition fit is not wanted, add "Fo" in the designation. These studs have thread tolerance class 6g on both ends and can be supplied as specials. Studs according to DIN 938 with a metal end $\approx 1d$ have many applications, but are mainly intended for use in steel counterparts.

Specifica tecnica

b	30
$b_m \approx 1d$	12
$b = L - (x + 3)$ up to $L \leq$	35
d-D	M12
L (mm)	70
P	1.75
x	4.3

Disegno tecnico

