

Hexagon head bolt oversized thread DIN 931 Steel Hot dip galvanized 8.8 M16X110

Numero articolo	01420.160.110
Marchio	-
UBB	952351331964
UNSPSC	31161620
EAN	8715492411365
PKG. di 25	Solo full box

Parametri tecnici:

Standard

Diametro	M16	ISO	4014
Lunghezza	110 mm	NEN	1555
Class	8.8	ASME	B18.2.3.1M
Driving features	Hexagon	DIN	931
Head shape	Hexagon head	NF	E25-112
Material	Steel		
Thread direction	Right		
Surface treatment	Hot dip galvanized		
Thread	Metric thread		

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	110
P	2
s	24

