



Spring-type straight pin slotted, heavy duty, stainless spring steel DIN ≈1481 Stainless spring steel 3,5X12MM

Numero articolo 51428.035.012

Marchio -

UBB 500635838229

UNSPSC 31163201

EAN 8717077785625

PKG. di 1000 Solo full box

Parametri tecnici:

Standard

Diametro	3.5 mm	DIN	≈1481
Lunghezza	12 mm	ISO	≈8752
Material	Stainless spring steel	BS	≈7060
Info	Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 8$ mm a single chamfer configuration is optional at the discretion of the manufacturer. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these	NEN	≈2458

FABORY pins are employed
with bolted joints the
below arrangement
should be used:

Specifica tecnica

a	0.6
d1 (max.)	4
d1 (min.)	3.8
d2 ≈	2.3
D (mm)	3.5
L (mm)	12
s	0.75

Disegno tecnico

