

Hexagon head bolt oversized thread DIN 931 Steel Hot dip galvanized 8.8 M24X70

Numero articolo	01420.240.070
Marchio	-
UBB	500621737732
UNSPSC	31161620
EAN	8715494504386
PKG. di 25	Solo full box

Parametri tecnici:

Standard

Diametro	M24	ISO	4014
Lunghezza	70 mm	DIN	931
Class	8.8	ASME	B18.2.3.1M
Driving features	Hexagon	NEN	1555
Head shape	Hexagon head	NF	E25-112
Material	Steel		
Thread direction	Right		
Surface treatment	Hot dip galvanized		
Thread	Metric thread		

Info
Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Specifica tecnica

Disegno tecnico

b (min.): 125mm $L \leq 200$ mm	60
b (min.): $L > 200$ mm	73
b (min.): $L \leq 125$ mm	54
d-D	M24
k	15
L (mm)	70
P	3
s	36

