



# SAFETY DATA SHEET

7100/7100NS Hard-Hat® Floorpaint

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**Product name and/or code** : 7100/7100NS Hard-Hat® Floorpaint

**Manufacturer** : Rust-Oleum Netherlands BV, PO. Box 138, NL-4700 AC Roosendaal, The Netherlands  
NV Martin Mathys, Kolenbergstraat 23, B-3545 Zelem, Belgium

**Emergency phone number** : Rust-Oleum: +31(0)165-593636; Fax +31(0)165-593600  
Martin Mathys: +32(0)13-460200; Fax +32(0)13-460201

**e-Mail address of person responsible for this SDS** : rpmeurohas@ro-m.com

**Product use** : Paint.

## 2. HAZARDS IDENTIFICATION

The product is classified as dangerous according to Directive 67/548/EEC and its amendments.

**Classification** : R10  
R66  
R52/53

**Physical/chemical hazards** : Flammable.

**Human health hazards** : Repeated exposure may cause skin dryness or cracking.

**Environmental hazards** : Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**Additional warning phrases** : Contains 2-butanone oxime. May produce an allergic reaction.

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substances presenting a health or environmental hazard within the meaning of the Dangerous Substances Directive 67/548/EEC.

Chemical name	CAS #	%	EU no.	Classification
naphtha (petroleum), hydrotreated heavy	64742-48-9	25 - 50	265-150-3	R10 Xn; R65 R66 [1] [2]
zinc oxide	1314-13-2	1 - 2.5	215-222-5	N; R50/53 [1]
naphtha (petroleum), hydrotreated heavy	64742-48-9	1 - 2.5	265-150-3	Xn; R65 R66 [1] [2]
solvent naphtha (petroleum), light arom.	64742-95-6	0 - 1	265-199-0	R10 Xn; R65 Xi; R37 R66 [1] [2]
1,2,4-trimethylbenzene	95-63-6	0 - 1	202-436-9	N; R51/53 R10 Xn; R20 Xi; R36/37/38 N; R51/53 [1] [2]
See section 16 for the full text of the R-phrases declared above				

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

Occupational exposure limits, if available, are listed in section 8.

## 4. FIRST AID MEASURES

### First aid measures

**General** : In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.

**Inhalation** : Remove to fresh air. Keep person warm and at rest. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. Give nothing by mouth. If unconscious, place in recovery position and seek medical advice.

**Skin contact** : Remove contaminated clothing and shoes. Wash skin thoroughly with soap and water or use recognized skin cleanser. Do not use solvents or thinners.

**Eye contact** : Check for and remove any contact lenses. Immediately flush eyes with running water for at least 15 minutes, keeping eyelids open.

## 4. FIRST AID MEASURES

- Ingestion** : If swallowed, seek medical advice immediately and show this container or label. Keep person warm and at rest. Do not induce vomiting.

## 5. FIRE-FIGHTING MEASURES

- Extinguishing media** : Recommended: alcohol-resistant foam, CO<sub>2</sub>, powders, water spray.  
Not to be used : water jet.
- Recommendations** : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard. Appropriate breathing apparatus may be required. Cool closed containers exposed to fire with water. Do not release runoff from fire to drains or watercourses.
- Hazardous combustion products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide  
metal oxide/oxides

## 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions** : Exclude sources of ignition and ventilate the area. Avoid breathing vapor or mist. Refer to protective measures listed in sections 7 and 8.
- Spill** : Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see section 13). Do not allow to enter drains or watercourses. Preferably clean with a detergent. Avoid using solvents. If the product contaminates lakes, rivers, or sewers, inform the appropriate authorities in accordance with local regulations.

**Note:** see section 8 for personal protective equipment and section 13 for waste disposal.

## 7. HANDLING AND STORAGE

- Handling** : Vapors are heavier than air and may spread along floors. Vapors may form explosive mixtures with air. Prevent the creation of flammable or explosive concentrations of vapors in air and avoid vapor concentrations higher than the occupational exposure limits.  
In addition, the product should only be used in areas from which all naked lights and other sources of ignition have been excluded. Electrical equipment should be protected to the appropriate standard.  
Keep container tightly closed. Keep away from heat, sparks and flame. No sparking tools should be used.  
Avoid contact with skin and eyes. Avoid the inhalation of dust, particulates, spray or mist arising from the application of this preparation. Avoid inhalation of dust from sanding.  
Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed.  
Put on appropriate personal protective equipment (see section 8).  
Always keep in containers made from the same material as the original one.  
Comply with the health and safety at work laws.
- Storage** : Store in accordance with local regulations. Observe label precautions. Do not store above the following temperature: 35°C (95°F). Store in a dry, cool and well-ventilated area. Keep away from heat and direct sunlight.  
Keep away from sources of ignition. Keep away from: oxidizing agents, strong alkalis, strong acids.  
No smoking. Prevent unauthorized access. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not empty into drains.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

- Engineering measures** : Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and solvent vapors below the OEL, suitable respiratory protection must be worn.

### Ingredient name

naphtha (petroleum), hydrotreated heavy

naphtha (petroleum), hydrotreated heavy

solvent naphtha (petroleum), light aromatic

1,2,4-trimethylbenzene

### Occupational exposure limits

**EH40/2005 WELs (United Kingdom (UK), 8/2007).**

STEL: 850 mg/m<sup>3</sup>, (as turpentine (150 ppm)) 15 minute(s). Form: Vapor  
TWA: 566 mg/m<sup>3</sup>, (as turpentine (100 ppm)) 8 hour(s). Form: Vapor

**EH40/2005 WELs (United Kingdom (UK), 8/2007).**

STEL: 850 mg/m<sup>3</sup>, (as turpentine (150 ppm)) 15 minute(s). Form: Vapor  
TWA: 566 mg/m<sup>3</sup>, (as turpentine (100 ppm)) 8 hour(s). Form: Vapor

**EH40/2005 WELs (United Kingdom (UK), 8/2007).**

TWA: 125 mg/m<sup>3</sup>, (Trimethylbenzene (25 ppm)) 8 hour(s). Form: Vapor  
**EH40/2005 WELs (United Kingdom (UK), 8/2007).**

TWA: 125 mg/m<sup>3</sup> 8 hour(s).

TWA: 25 ppm 8 hour(s).

### Exposure controls/personal protection

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

<b>Occupational exposure controls</b>	: Use only with adequate ventilation. Use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. The engineering controls also need to keep gas, vapor or dust concentrations below any lower explosive limits. Use explosion-proof ventilation equipment.
<b>Hygiene measures</b>	: Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
<b>Respiratory protection</b>	: Recommended: organic vapor filter (Type A) .
<b>Hand protection</b>	: >8 hours (breakthrough time): For prolonged or repeated handling, use the following type of gloves: nitrile rubber or neoprene (EN 374). <i>Barrier creams may help to protect the exposed areas of the skin but should not be applied once exposure has occurred. The user must check that the final choice of type of glove selected for handling this product is the most appropriate and takes into account the particular conditions of use, as included in the user's risk assessment.</i>
<b>Eye protection</b>	: Recommended: safety glasses with side-shields (EN 166).
<b>Skin protection</b>	: Recommended: disposable overall .
<b>Environmental exposure controls</b>	: Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state</b>	: Liquid.
<b>Odor</b>	: Hydrocarbon. [Slight]
<b>Color</b>	: Depending on productnumber
<b>Flash point</b>	: Closed cup: 40°C (104°F) [ISO EN DIN 1523 / DIN 53213-1]
<b>Boiling point</b>	: > 160 °C
<b>Explosion limits</b>	: Lower: 0.6% Upper: 8%
<b>Vapor pressure</b>	: 0,7 kPa (5,25 mm Hg)
<b>Vapor density</b>	: >1 (Air = 1)
<b>Evaporation rate (BuAc=1)</b>	: 0,2 (Butyl acetate. = 1)
<b>Volatility %</b>	: 52 to 58.5% (v/v). 34 to 48% (w/w).
<b>Viscosity</b>	: Dynamic: 450 to 1200 mPa·s (450 to 1200 cP)
<b>Relative density (kg/L)</b>	: 0,94 to 1,17

## 10. STABILITY AND REACTIVITY

Stable under recommended storage and handling conditions (see section 7).

Hazardous decomposition products: carbon monoxide, carbon dioxide, smoke, oxides of nitrogen.

Keep away from the following materials to prevent strong exothermic reactions: oxidizing agents, strong alkalis, strong acids.

## 11. TOXICOLOGICAL INFORMATION

There is no data available on the preparation itself. The preparation has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and classified for toxicological hazards accordingly. See sections 3 and 15 for details.

Exposure to component solvent vapor concentrations in excess of the stated occupational exposure limit may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Solvents may cause some of the above effects by absorption through the skin. Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and, in extreme cases, loss of consciousness. Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin, resulting in non-allergic contact dermatitis and absorption through the skin. If splashed in the eyes, the liquid may cause irritation and reversible damage.

Contains 2-butanone oxime. May produce an allergic reaction.

### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
naphtha (petroleum), hydrotreated heavy	LD50 Dermal	Rabbit	>3000 mg/kg	-
	LD50 Oral	Rat	>15000 mg/kg	-
	LC50 Inhalation	Rat	>5.5 mg/L	4 hours
	Vapor			
zinc oxide	LD Intratracheal	Rat	>4979 ug/kg	-
	LD Oral	Rat	>8437 mg/kg	-
	LD50 Intraperitoneal	Rat	>240 mg/kg	-
	LC50 Inhalation Dusts and mists	Mouse	2500 mg/m³	4 hours
	LD50 Dermal	Rabbit	>3000 mg/kg	-
naphtha (petroleum), hydrotreated heavy	LD50 Dermal	Rabbit	>3000 mg/kg	-

**11. TOXICOLOGICAL INFORMATION**

solvent naphtha (petroleum), light aromatic	LD50 Oral	Rat	>5000 mg/kg	-
	LC50 Inhalation Vapor	Rat	>5.5 mg/L	4 hours
	LD50 Dermal	Rabbit	>2000 mg/kg	-
1,2,4-trimethylbenzene	LD50 Oral	Mouse	8400 mg/kg	-
	LD50 Oral	Rat	8400 mg/kg	-
	LC50 Inhalation Vapor	Rat	29 mg/L	4 hours
	LD50 Oral	Rat	5 gm/kg	-
	LDLo Intraperitoneal	Rat	1752 mg/kg	-
	LC50 Inhalation Vapor	Rat	18000 mg/m3	4 hours
	LC50 Inhalation Vapor	Rat	18000 mg/m³	4 hours

**12. ECOLOGICAL INFORMATION**

There is no data available on the preparation itself.  
Do not allow to enter drains or watercourses.

The preparation has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and is classified for eco-toxicological properties accordingly. See sections 2 and 15 for details.

**Aquatic ecotoxicity**

Ingredient name	Result	Species	Exposure
naphtha (petroleum), hydrotreated heavy	Acute EC50 >1000 mg/L	Daphnia	4 hours
zinc oxide	Acute IC50 >1000 mg/L	Algae	4 hours
	Acute LC50 >1000 mg/L	Fish	4 hours
	Acute EC50 >1000 ppm Fresh water	Daphnia - Water flea - Daphnia magna - <24 hours	48 hours
	Acute LC50 >320 ppm Fresh water	Fish - Bluegill - Lepomis macrochirus	96 hours
	Acute LC50 1.1 to 2.5 ppm Fresh water	Fish - Rainbow trout, donaldson trout - Oncorhynchus mykiss	96 hours
	Acute LC50 24600 ug/L Fresh water	Daphnia - Water flea - Daphnia magna - Neonate - <24 hours	48 hours
	Acute LC50 2246000 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - Neonate - <24 hours	96 hours
naphtha (petroleum), hydrotreated heavy	Acute EC50 >1000 mg/L	Daphnia	4 hours
solvent naphtha (petroleum), light aromatic	Acute IC50 >1000 mg/L	Algae	4 hours
	Acute LC50 >1000 mg/L	Fish	4 hours
	Acute IC50 1 to 10 mg/L	Algae	72 hours
1,2,4-trimethylbenzene	Acute LC50 18 mg/L	Fish - Trout - Oncorhynchus	96 hours
	Acute LC50 21 mg/L	Daphnia	24 hours
	Acute EC50 30 mg/L	Daphnia	48 hours
	Acute LC50 7720 to 8280 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - 34 days	96 hours
	Acute LC50 17000 ug/L Marine water	Crustaceans - Dungeness or edible crab - Cancer magister - Zoa	48 hours

**Ecological information****Biodegradability**

**Conclusion/Remark** : Not available.

Ingredient name	Aquatic half-life	Photolysis	Biodegradability
naphtha (petroleum), hydrotreated heavy	Fresh water <28 days	-	Readily
naphtha (petroleum), hydrotreated heavy	Fresh water <28 days	>50%; < 28 day(s).	Readily
solvent naphtha (petroleum), light aromatic	-	-	Readily

**Bioaccumulative potential**

Ingredient name	LogP <sub>ow</sub>	BCF	Potential
naphtha (petroleum), hydrotreated heavy	4.9 to 6.5	-	high
solvent naphtha (petroleum), light aromatic	3.7 to 4.5	-	high
1,2,4-trimethylbenzene	3.8	-	high

**13. DISPOSAL CONSIDERATIONS**

Do not allow to enter drains or watercourses.  
Dispose of according to all federal, state and local applicable regulations.


**European waste catalogue (EWC)** : The European Waste Catalogue classification of this product, when disposed of as waste, is: 08 01 11\* waste paint and varnish containing organic solvents or other dangerous substances. If this product is mixed with other wastes, this code may no longer apply. If mixed with other wastes, the appropriate code should be assigned. For further information, contact your local waste authority.

**Hazardous waste** : Yes.

## 14. TRANSPORT INFORMATION

**Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

### International transport regulations

Regulatory information	UN number	Proper shipping name	Classes	PG*	Label	Additional information
ADR/RID Class	-	-	-	-		<b>Remarks</b> Transport acc. ADR 2.2.3.1.5 [SP223]
IMDG Class	1263	Paint.	3	III		<b>Emergency schedules (EmS):</b> F-E + S-E  <b>Marine pollutant:</b> NO  <b>Remarks:</b> (≤ 30L: ) Transport acc. IMDG 2.3.2.5 [SP223]
IATA Class	1263	Paint.	3	III		<b>Passenger and Cargo Aircraft</b> Quantity limitation: 60 L Packaging instructions: 309 <b>Cargo Aircraft Only</b> Quantity limitation: 220 L Packaging instructions: 310 <b>Limited Quantities - Passenger Aircraft</b> Quantity limitation: 10 L Packaging instructions: Y 309

PG\* : Packing group

The "viscosity exemption" provisions do not apply to air transport.

## 15. REGULATORY INFORMATION

<b><u>EU regulations</u></b>	: The product is classified and labelled for supply in accordance with the Directive 1999/45/EC as follows:
<b>Risk phrases</b>	: R10- Flammable. R66- Repeated exposure may cause skin dryness or cracking. R52/53- Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
<b>Safety phrases</b>	: S2- Keep out of the reach of children. S23- Do not breathe vapor. S24- Avoid contact with skin. S46- If swallowed, seek medical advice immediately and show this container or label. S51- Use only in well-ventilated areas. S56- Dispose of this material and its container at hazardous or special waste collection point.
<b>VOC for Ready-for-Use Mixture</b>	: IIA/i. One-pack performance coatings. EU limit values: 600g/l (2007) 500g/l (2010.) This product contains a maximum of 485 g/l VOC.
<b>Europe inventory</b>	: At least one component is not listed.
<b><u>Other EU regulations</u></b>	
<b>Additional warning phrases</b>	: Contains 2-butanone oxime. May produce an allergic reaction.
<b>CN code</b>	: 3208 10 90

## 16. OTHER INFORMATION

<b>Full text of R-phrases referred to in sections 2 and 3 - United Kingdom (UK)</b>	: R10- Flammable. R20- Harmful by inhalation. R65- Harmful: may cause lung damage if swallowed. R37- Irritating to respiratory system. R36/37/38- Irritating to eyes, respiratory system and skin. R66- Repeated exposure may cause skin dryness or cracking. R50/53- Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R51/53- Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R52/53- Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
---	--

The information in this Safety Data Sheet is required pursuant to EU Directive 91/155/EEC and its amendments.

Indicates information that has changed from previously issued version.

### Notice to reader

**16. OTHER INFORMATION**

*The information in this SDS is based on the present state of our knowledge and on current laws. The product is not to be used for purposes other than those specified under section 1 without first obtaining written handling instructions. It is always the responsibility of the user to take all necessary steps to fulfill the demands set out in the local rules and legislation. The information in this SDS is meant to be a description of the safety requirements for our product. It is not to be considered a guarantee of the product's properties. ©Copyright by Rust-Oleum Netherlands B.V. / Martin Mathys B.V.*



<b>Version</b>	1.02	v.4.0.	<i>Page: 6/6</i>
<b>Date of issue</b>	31-08-2009.		<i>Printed 10-11-2009.</i>