



Hexagon thin nut ISO 4035 Steel Hot dip galvanized 04 ISO metric M20

Numero articolo	01587.200.001
-----------------	---------------

Marchio	-
---------	---

UBB	500621920965
-----	--------------

UNSPSC	31161727
--------	----------

EAN	8715494514217
-----	---------------

PKG. di 100	Solo full box
-------------	---------------

Parametri tecnici:

Diametro	M20
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating. As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

Standard

ISO	4035
-----	------

as the thread will be
protected by the zinc
layer of the mating
part.ISO metric

Specifica tecnica

d-D	M20
m (max.)	10
P	2.5
s	30

Disegno tecnico

