

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

### 1 Identification of the substance/mixture and of the company/undertaking

- **Product identifier**
- **Trade name:** MOTIP HEAT RESISTANT LACQUER Silver
- **Article number:** 04032
- **Relevant identified uses of the substance or mixture and uses advised against**
- **Application of the substance / the preparation** Paint
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolfraamweg 2  
NL-8471 XC Wolvega  
The Netherlands  
Tel: +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail info@nl.motipdupli.com
- **Further information obtainable from:** QHSE Department
- **Emergency telephone number:** Tel: +31 (0)561 694400 (08.00 / 17.00)

### 2 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Aerosol 1 H222 Extremely flammable aerosol.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xi; Irritant

R36: Irritating to eyes.



F+; Extremely flammable

R12: Extremely flammable.

R66-67: Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness.

- **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

At long or repeated contact with skin it may cause dermatitis due to the degreasing effect of the solvent.

Warning! Pressurized container.

Has a narcotizing effect.

- **Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

(Contd. on page 2)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 1)

· **Label elements**

· **Labelling according to EU guidelines:**

The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

· **Code letter and hazard designation of product:**



Xi Irritant

F+ Extremely flammable

· **Risk phrases:**

- 12 Extremely flammable.
- 36 Irritating to eyes.
- 66 Repeated exposure may cause skin dryness or cracking.
- 67 Vapours may cause drowsiness and dizziness.

· **Safety phrases:**

- 2 Keep out of the reach of children.
- 16 Keep away from sources of ignition - No smoking.
- 23 Do not breathe aerosol.
- 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- 29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.
- 46 If swallowed, seek medical advice immediately and show this container or label.
- 51 Use only in well-ventilated areas.

· **Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### 3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2	acetone Xi R36 F R11 R66-67 Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	25-50%
CAS: 74-98-6 EINECS: 200-827-9	propane F+ R12 Flam. Gas 1, H220 Press. Gas, H280	12.5-20%

(Contd. on page 3)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

































Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 2)

CAS: 106-97-8 EINECS: 203-448-7	butane  F+ R12  Flam. Gas 1, H220  Press. Gas, H280	10-12.5%
CAS: 75-28-5 EINECS: 200-857-2	isobutane  F+ R12  Flam. Gas 1, H220  Press. Gas, H280	10-12.5%
CAS: 1330-20-7 EINECS: 215-535-7	xylene  Xn R20/21  Xi R38 R10  Flam. Liq. 3, H226  Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	5-10%
CAS: 100-41-4 EINECS: 202-849-4	ethylbenzene  Xn R20  F R11  Flam. Liq. 2, H225  Acute Tox. 4, H332	2.5-5%
CAS: 95-63-6 EINECS: 202-436-9	1,2,4-trimethylbenzene  Xn R20  Xi R36/37/38  N R51/53 R10  Flam. Liq. 3, H226  Aquatic Chronic 2, H411  Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335	1-2.5%
CAS: 64742-95-6 EINECS: 265-199-0	Solvent naphtha (petroleum), light arom.  Xn R65  Xi R37  N R51/53 R10-66-67  Flam. Liq. 3, H226  Asp. Tox. 1, H304  Aquatic Chronic 2, H411  STOT SE 3, H335+H336	1-2.5%
CAS: 108-67-8 EINECS: 203-604-4	mesitylene  Xi R37  N R51/53 R10  Flam. Liq. 3, H226  Aquatic Chronic 2, H411  STOT SE 3, H335	0.1-1%

(Contd. on page 4)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31















Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

Trade name: **MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 3)

CAS: 98-82-8 EINECS: 202-704-5	<b>cumene</b>  <b>Xn R65</b>  <b>Xi R37</b>  <b>N R51/53</b> <b>R10</b> <hr style="border-top: 1px dashed black;"/>  <b>Flam. Liq. 3, H226</b>  <b>Asp. Tox. 1, H304</b>  <b>Aquatic Chronic 2, H411</b>  <b>STOT SE 3, H335</b>	0.1-1%
CAS: 103-65-1 EINECS: 203-132-9	<b>propylbenzene</b>  <b>Xn R65</b>  <b>Xi R37</b>  <b>N R51/53</b> <b>R10</b> <hr style="border-top: 1px dashed black;"/>  <b>Flam. Liq. 3, H226</b>  <b>Asp. Tox. 1, H304</b>  <b>Aquatic Chronic 2, H411</b>  <b>STOT SE 3, H335</b>	0.1-1%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

### 4 First aid measures

- **Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### 5 Firefighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**  
Ensure adequate ventilation  
Keep away from ignition sources.
- **Environmental precautions:**  
Do not allow product to reach sewage system or any water course.  
Inform respective authorities in case of seepage into water course or sewage system.  
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **Reference to other sections**  
See Section 7 for information on safe handling.

(Contd. on page 5)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 4)

See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### 7 Handling and storage

- **Handling:**
- **Precautions for safe handling**  
No special measures required.  
Ensure good ventilation/exhaustion at the workplace.  
Open and handle receptacle with care.
- **Information about fire - and explosion protection:**  
Do not spray onto a naked flame or any incandescent material.  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.  
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Store in a cool location.  
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**  
Keep container tightly sealed.  
Protect from heat and direct sunlight.
- **Specific end use(s)** No further relevant information available.

### 8 Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **Control parameters**

#### Ingredients with limit values that require monitoring at the workplace:

##### 67-64-1 acetone

WEL Short-term value: 3620 mg/m<sup>3</sup>, 1500 ppm  
Long-term value: 1210 mg/m<sup>3</sup>, 500 ppm

##### 106-97-8 butane

WEL Short-term value: 1810 mg/m<sup>3</sup>, 750 ppm  
Long-term value: 1450 mg/m<sup>3</sup>, 600 ppm  
Carc (if more than 0.1% of buta-1.3-diene)

##### 1330-20-7 xylene

WEL Short-term value: 441 mg/m<sup>3</sup>, 100 ppm  
Long-term value: 220 mg/m<sup>3</sup>, 50 ppm  
Sk; BMGV

##### 100-41-4 ethylbenzene

WEL Short-term value: 552 mg/m<sup>3</sup>, 125 ppm  
Long-term value: 441 mg/m<sup>3</sup>, 100 ppm

##### 95-63-6 1,2,4-trimethylbenzene

WEL Long-term value: 125 mg/m<sup>3</sup>, 25 ppm  
ILV

- **Additional information:** The lists valid during the making were used as basis.

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

Trade name: **MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 5)

- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing  
Wash hands before breaks and at the end of work.  
Do not inhale gases / fumes / aerosols.  
Avoid contact with the eyes.  
Avoid contact with the eyes and skin.
- **Respiratory protection:** Not required.
- **Protection of hands:** Not required.
- **Material of gloves:** Not required.
- **Penetration time of glove material:** Not required.
- **Eye protection:**



Tightly sealed goggles

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**
  - Form:** Aerosol
  - Colour:** According to product specification
- **Odour:** Characteristic
- **Odour threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**
  - Melting point/Melting range:** Undetermined.
  - Boiling point/Boiling range:** Not applicable, as aerosol.
- **Flash point:**
  - < 0°C (< 32°F)
  - Not applicable, as aerosol.
- **Ignition temperature:** 365°C (689°F)
- **Decomposition temperature:** Not determined.
- **Self-igniting:** Product is not selfigniting.
- **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
- **Explosion limits:**
  - Lower:** 1.5 Vol %
  - Upper:** 13.0 Vol %
- **Vapour pressure at 20°C (68°F):** 3500 hPa (2625 mm Hg)
- **Density at 20°C (68°F):** 0.695 g/cm<sup>3</sup> (5.8 lbs/gal)
- **Relative density:** Not determined.
- **Vapour density:** Not determined.
- **Evaporation rate:** Not applicable.
- **Solubility in / Miscibility with water:** Not miscible or difficult to mix.

(Contd. on page 7)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

Trade name: **MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 6)

- |   |                 |
|---|-----------------|
| · <b>Segregation coefficient (n-octanol/water):</b> Not determined.   |                 |
| · <b>Viscosity:</b>   |                 |
| Dynamic:  | Not determined. |
| Kinematic:  | Not determined. |
| · <b>Solvent content:</b>   |                 |
| Organic solvents:   | 95.6 %          |
| EU-VOC:   | 695.0 g/l       |
| EU-VOC in %:  | 100.00 %        |
| · <b>Solids content:</b> 4.4 %  |                 |
| · <b>Other information</b> No further relevant information available. |                 |

### 10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

### 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

- **LD/LC50 values relevant for classification:**

#### 67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
Dermal	LD50	20000 mg/kg (rabbit)
	LC50 / 4 h	39 mg/m3 (rat)

#### 106-97-8 butane

	LC50 / 4 h	658 mg/m3 (rat)
--	------------	-----------------

#### 1330-20-7 xylene

Oral	LD50	4300 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
	LC50 / 4 h	22.1 mg/m3 (rat)

#### 100-41-4 ethylbenzene

Oral	LD50	3500 mg/kg (rat)
Dermal	LD50	17800 mg/kg (rabbit)

#### 95-63-6 1,2,4-trimethylbenzene

Oral	LD50	5000 mg/kg (rat)
------	------	------------------

#### 64742-95-6 Solvent naphtha (petroleum), light arom.

Oral	LD50	3592 mg/kg (rat) (OECD401)
Dermal	LD50	>3160 mg/kg (rab) (OECD402)
	LC50 / 4 h	>15 mg/m3 (rat)

#### 64742-48-9 Naphtha (petroleum), hydrotreated heavy

Oral	LD50	>15000 mg/kg (rat)
------	------	--------------------

(Contd. on page 8)



# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 7)

Dermal	LD50	>3000 mg/kg (rab)
	LC50 / 4 h	>2.8 mg/m <sup>3</sup> (rat)

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**  
The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:  
Irritant

## 12 Ecological information

### · Toxicity

#### · Aquatic toxicity:

##### 67-64-1 acetone

EC50 / 48 h	39 mg/l (daphnia magna)
LC50 / 48 h	2262 mg/l (daphnia magna)
LC50 / 96 h (static)	5540 mg/l (fish)

##### 1330-20-7 xylene

EC50 / 48 h	7.4 mg/l (daphnia magna)
LC50 / 96 h	13.5 mg/l (fish)

##### 64742-95-6 Solvent naphtha (petroleum), light arom.

EC50 / 24 h	150 mg/l (daphnia magna)
EC50 / 48 h	7.4 mg/l (daphnia magna)
LC50 / 96 h	3.77 mg/l (fish)

##### 64742-48-9 Naphtha (petroleum), hydrotreated heavy

LC50 / 96 h	>100 mg/l (fish)
-------------	------------------

- **Persistence and degradability** No further relevant information available.
- **Behaviour in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.  
Danger to drinking water if even small quantities leak into the ground.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

#### · European waste catalogue

08 01 11*	waste paint and varnish containing organic solvents or other dangerous substances
15 01 04	metallic packaging

(Contd. on page 9)



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

Trade name: **MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 8)

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

## 14 Transport information

- **Land transport ADR/RID (cross-border)**



- **ADR/RID class:** 2 5F Gases.
- **Danger code (Kemler):** -
- **UN-Number:** 1950
- **Packaging group:** -
- **Hazard label** 2.1
- **UN proper shipping name:** 1950 AEROSOLS
- **Limited quantities (LQ)** LQ2
- **Transport category** 2
- **Tunnel restriction code** D

- **Maritime transport IMDG:**



- **IMDG Class:** 2.1
- **UN Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **EMS Number:** F-D,S-U
- **Marine pollutant:** No
- **Proper shipping name:** AEROSOLS

- **Air transport ICAO-TI and IATA-DGR:**



- **ICAO/IATA Class:** 2.1
- **UN/ID Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **Proper shipping name:** AEROSOLS, flammable

- **UN "Model Regulation":** UN1950, AEROSOLS, 2.1
- **Special precautions for user** Warning: Gases.
- **Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code** Not applicable.

## 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Labelling according to EU guidelines:**  
The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

(Contd. on page 10)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 9)

**· Code letter and hazard designation of product:***Xi Irritant**F+ Extremely flammable***· Risk phrases:**

- 12 Extremely flammable.
- 36 Irritating to eyes.
- 66 Repeated exposure may cause skin dryness or cracking.
- 67 Vapours may cause drowsiness and dizziness.

**· Safety phrases:**

- 2 Keep out of the reach of children.
- 16 Keep away from sources of ignition - No smoking.
- 23 Do not breathe aerosol.
- 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- 29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.
- 46 If swallowed, seek medical advice immediately and show this container or label.
- 51 Use only in well-ventilated areas.

**· Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

**· Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

**· Relevant phrases**

- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.
- R10 Flammable.
- R11 Highly flammable.
- R12 Extremely flammable.
- R20 Harmful by inhalation.
- R20/21 Harmful by inhalation and in contact with skin.
- R36 Irritating to eyes.
- R36/37/38 Irritating to eyes, respiratory system and skin.
- R37 Irritating to respiratory system.
- R38 Irritating to skin.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R66 Repeated exposure may cause skin dryness or cracking.

(Contd. on page 11)

**Safety data sheet**  
**according to 1907/2006/EC, Article 31**

Printing date 23.03.2011

Version number 40

Revision: 23.03.2011

**Trade name: MOTIP HEAT RESITANT LACQUER Silver**

(Contd. of page 10)

R67      Vapours may cause drowsiness and dizziness.

· **Department issuing MSDS:** QHSE Department

· **Contact:**

Mrs. D. Kleistra

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

· **\* Data compared to the previous version altered.**

GB