

Spring-type straight pin slotted, heavy duty ISO 8752 Spring steel 420-560 HV30 Zinc plated 8X20MM



Numero articolo 39105.080.020

Marchio -

UBB 500649082913

UNSPSC 31163201

EAN 8717077256712

PKG. di 100 Solo full box

Parametri tecnici:

Diametro	8 mm
Lunghezza	20 mm
Material	Spring steel
Material technical	420-560 HV30
Surface treatment	Zinc plated

Standard

NEN	2458
DIN	1481
ISO	8752
BS	7060

Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction

elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Specifica tecnica

a (min.)	1.6
d1 (max.)	8.8
d1 (min.)	8.5
d2 ≈	5.5
D (mm)	8
L (mm)	20
s	1.5
V	42.76

Disegno tecnico

