



Lage zeskantmoer MF DIN 439 2 Roestvaststaal (RVS) A2 Min.50 M16X1,50

Artikelnummer 51092.160.150

Merk -

UBB 950355569431

UNSPSC 31161727

EAN 8715492268211

PKG. van 50 Alleen volledige verpakkingen

Technische parameters

Diameter	M16
Klasse	Min.50
Aandraaivoorziening	Zeskant
Materiaalsoort	Roestvaststaal
Materiaalsoort Technisch	A2
Draadrichting	Rechts
Draadsoort	Metrisch fijne schroefdraad

Info

do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr,

Standaarden

NF	E25-453
NEN	2334-B
ASME	B18.2.4.5M
ISO	8675
DIN	439-2

N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische specificatie

d-D	M16
m	8
P	1.5
s	24

Technische tekening

