

HANDTOOL THR INS TP6102 M12



Numero articolo 71580.120.001

Marchio -

UBB 500505986926

UNSPSC 31162802

EAN 8715494295581

PKG. di 1 Solo full box

Parametri tecnici:

Diametro	M12
For nom. size	12mm
For nom. size d1	12
Material	Steel
Surface treatment	Plain
Tipo no.	6102

Standard

Info	<p>Advantages of the hand- and machine tool for self-cutting threaded inserts with hexagon socket: The insert doesn't have to be screwed onto the tool: saves up to 50% assembly time. The insert can simply be assembled with this tool: use with tap wrench or with screw machine. The insertion tool only needs to turn clockwise. The insert is easily removed by unscrewing. Tool exclusively for machine insertion or manual insertion (with the aid of a tap wrench or an open-ended spanner)</p>
------	--

of self-tapping
thread inserts with
hexagonal socket
types 302 2 and 308
2.d1 = tool fit for this
inner diameter of the
insert.s = nominal
socket width across
flats of the insert.G
= drive square width
across flats.

Specifica tecnica

B	125
F	14
G	11
s	10.1

Disegno tecnico

