



Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Low carbon steel Zinc plated #8-32X2.

Numero articolo	U24522.016.0200
Marchio	-
UBB	500624939400
UNSPSC	31161504
EAN	8717077793088
PKG. di 100	Solo full box

Parametri tecnici:

Diametro	NO.8
Lunghezza	2 Inch
Driving features	Phillips
Head shape	Pan head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	32

Info

Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standard

ASME B18.6.3

Specifica tecnica

A (max.)	0.322
H (max.)	0.115

Disegno tecnico

FABORY

