



Lage zeskantmoer MF DIN 439 2 Roestvaststaal (RVS) A2 Min.50 M22X2,00

Artikelnummer	51092.220.200
Merk	-
UBB	500571314714
UNSPSC	31161727
EAN	8715494139557
PKG. van 25	Alleen volledige verpakkingen

Technische parameters

Diameter	M22
Klasse	Min.50
Aandraaivoorziening	Zeskant
Materiaalsoort	Roestvaststaal
Materiaalsoort Technisch	A2
Draadrichting	Rechts
Draadsoort	Metrisch fijne schroefdraad

Info

do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr,

Standaarden

NF	E25-453
ASME	B18.2.4.5M
ISO	8675
DIN	439-2
NEN	2334-B

N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische specificatie

d-D	M22
m	11
P	2
s	32

Technische tekening

