

Hexagon head bolt for pressure vessels ISO 4014 Stal (AD-W7) Ocynkowane 5.6 M10X90

Numer artykułu	08751.100.090
Marka	-
UBB	500648335726
UNSPSC	31161620
Numer EAN	8717077214736
Opakowanie 100	Tylko pełne opakowanie

Parametry techniczne

Diameter	M10
Length	90 mm
Klasa	5.6
Gniazdo	Hexagon
Kształt łba	Łeb sześciokątny
Materiał	Stal (AD-W7)
Kierunek gwintu	Prawy
Obróbka powierzchni	Ocynkowane
Gwint	Metryczny

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are

Normy

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555

entitled to replace a
certificate EN 10204
3.1 by marking the
fasteners with the
property class and
the manufacturer's
mark. This
recognition is equally
accepted by Lloyd's
Register Energy.do
zbiorników
ciśnieniowych

Specyfikacja techniczna

b (min.): 125mm $L \leq 200$ mm	32
------------------------------------	----

b (min.): $L > 200$ mm	45
------------------------	----

b (min.): $L \leq 125$ mm	26
---------------------------	----

d-D	M10
-----	-----

k	6.4
---	-----

L (mm)	90
--------	----

P	1.5
---	-----

s	17
---	----

Rysunek techniczny

