



Lage zeskantmoer MF DIN 439 2 Roestvaststaal (RVS) A2 Min.50 M27X1,50

Artikelnummer	51092.270.150
---------------	---------------

Merk	-
------	---

UBB	950355569928
-----	--------------

UNSPSC	31161727
--------	----------

EAN	8715492268273
-----	---------------

PKG. van 3	Alleen volledige verpakkingen
------------	-------------------------------

Technische parameters

Diameter	M27
Klasse	Min.50
Aandraaivoorziening	Zeskant
Materiaalsoort	Roestvaststaal
Materiaalsoort Technisch	A2
Draadrichting	Rechts
Draadsoort	Metrisch fijne schroefdraad

Standaarden

ISO	8675
NEN	2334-B
NF	E25-453
ASME	B18.2.4.5M
DIN	439-2

Info	do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr,
------	--

N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische specificatie

d-D	M27
m	13.5
P	1.5
s	41

Technische tekening

