FABORY



Sprężyny **talerzowe do** zastosowań **krytycznych, typ A** (powiększone) **EN 16983 A Stal acc. to EN 16983 Fosfatowane 180X92,0X10,0MM**

Numer artykułu	36300.988.100
Marka	-
UBB	500644901919
UNSPSC	31161811
Numer EAN	8717077039599
Opakowanie 1	Tylko pełne opakowanie

Parametry techniczne

Diameter	92 mm
d_e	180
di	92
Materiał	Stal
Materiał techniczny	acc. to EN 16983
Średnica zewnętrzna	180
Obróbka powierzchni	Fosfatowane
Typ nr.	A
Info	Warning: electroplating of these products may cause hydrogen embrittlement.F = spring load in Newton at a deflection s ≈ 0,75 h0 (h0 = l0 - t).The values specified for t are nominal values. In the case of springs with 6 < t ≤ 14 the desired spring load F is to be obtained

Normy

DIN	2093-A
EN	16983-A

	by reducing the thickness of single disc springs t to the values between brackets.Refer to EN 16984 for calculation of disc springs.Extensive technical data available on request.

Specyfikacja techniczna

di (H12)	92
D (mm)	92
F	125417
l0	14
t	10
Grubość	10

Rysunek techniczny

