



## 20X160

Cod Articol	45800FIS
Marcă	-
UBB	500616731203
UNSPSC	31162101
EAN	4006209458006
PKG. of 1	Exclusiv împachetare

### Parametri tehnici

Caracteristici cheie	<p>Functioning - The FWA is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS setting tool.</p>
----------------------	---

### Standarde

Info	<p>do = Nominal diameter of drill  bit.tfix = Grip range.hef = Effective anchorage</p>
------	--

depth.Min. td =  
Recommended  
drilling depth.kN  
= Load in kN.The  
allowable load is  
valid for one single  
anchor, at cracked  
concrete (tensile  
zone) with concrete  
class C20/25, incl.  
partial safety factor  
 $\gamma_f = 1,4$  and if the  
Scr, N and Ccr,  
N are taken in to  
account.When  
reduction on spacing  
and edge distance  
take place a re-  
calculation of forces  
should be carried out  
by making use of the  
technical guide or  
calculation software,  
they are available  
on request.Final  
calculations should  
comply with the  
complete European  
Technical Approval  
(ETA), this approval  
is also available on  
request.

## Specificatii tehnice

## Desen tehnic

