

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

1 Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** MOTIP EGR CLEANER
- **Article number:** 090516
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Preparation
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolframweg 2
NL- 8471 XC Wolvega
The Netherlands
Tel: +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail info@nl.motipdupli.com
- **Further information obtainable from:** QHSE Department
- **1.4 Emergency telephone number:** +31 629058130 (24 h/d, 7 d/wk)

2 Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS07

Skin Irrit. 2	H315	Causes skin irritation.
Eye Irrit. 2	H319	Causes serious eye irritation.
STOT SE 3	H336	May cause drowsiness or dizziness.
Aquatic Chronic 3	H412	Harmful to aquatic life with long lasting effects.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xn; Harmful

R20/21: Harmful by inhalation and in contact with skin.



Xi; Irritant

R36/38: Irritating to eyes and skin.



F+; Extremely flammable

R12: Extremely flammable.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

- **Information concerning particular hazards for human and environment:**
The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 1)

*Warning! Pressurized container.***· Classification system:***The classification is according to the latest editions of the EU-lists, and extended by company and literature data.***· 2.2 Label elements****· Labelling according to Regulation (EC) No 1272/2008***The product is classified and labelled according to the CLP regulation.***· Hazard pictograms**

GHS02 GHS07

· Signal word Danger**· Hazard-determining components of labelling:***Naphtha (petroleum), hydrotreated light (< 0,1 % benzol CAS nr. 71-43-2)**butanone**propan-2-ol***· Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H315 Causes skin irritation.**H319 Causes serious eye irritation.**H336 May cause drowsiness or dizziness.**H412 Harmful to aquatic life with long lasting effects.***· Precautionary statements***P101 If medical advice is needed, have product container or label at hand.**P102 Keep out of reach of children.**P103 Read label before use.**P260 Do not breathe spray.**P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.**P251 Pressurized container: Do not pierce or burn, even after use.**P211 Do not spray on an open flame or other ignition source.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents/container in accordance with local regulations.***· 2.3 Other hazards****· Results of PBT and vPvB assessment****· PBT:** *Not applicable.***· vPvB:** *Not applicable.*

3 Composition/information on ingredients

· 3.2 Chemical characterization: Mixtures**· Description:** *Mixture of substances listed below with nonhazardous additions.***· Dangerous components:**

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 2)

CAS: 1330-20-7 EINECS: 215-535-7 Index number: 601-022-00-9 Reg.nr.: 01-2119488216-32	xylene  Xn R20/21  Xi R38 R10  Flam. Liq. 3, H226  Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	12.5-20%
CAS: 78-93-3 EINECS: 201-159-0 Index number: 606-002-00-3 Reg.nr.: 01-2119457290-43-xxxx	butanone  Xi R36  F R11 R66-67  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	12.5-20%
CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25-xxxx	propan-2-ol  Xi R36  F R11 R67  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	12.5-20%
CAS: 64742-49-0 EC number: 921-024-6 Index number: 649-328-00-1 Reg.nr.: 01-2119475514-35-xxxx	Naphtha (petroleum), hydrotreated light (< 0,1 % benzol CAS nr. 71-43-2)  Xn R65  Xi R38  F R11  N R51/53 R67  Flam. Liq. 2, H225  Asp. Tox. 1, H304  Aquatic Chronic 2, H411  Skin Irrit. 2, H315; STOT SE 3, H336	12.5-20%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21-xxxx	propane  F+ R12  Flam. Gas 1, H220 Press. Gas, H280	5-10%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32-xxxx	butane  F+ R12  Flam. Gas 1, H220 Press. Gas, H280	5-10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27-xxxx	isobutane  F+ R12  Flam. Gas 1, H220 Press. Gas, H280	5-10%

Regulation (EC) No 648/2004 on detergents / Labelling for contents

aliphatic hydrocarbons	≥ 30%
aromatic hydrocarbons	15 - 30%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

4 First aid measures

· 4.1 Description of first aid measures

· General information:

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 3)

- **After inhalation:**
Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Keep away from ignition sources.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
Do not spray onto a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Store in a cool location.
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Protect from heat and direct sunlight.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 4)

· **7.3 Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· 8.1 Control parameters

· **Ingredients with limit values that require monitoring at the workplace:**

1330-20-7 xylene

WEL () Short-term value: 441 mg/m³, 100 ppm
Long-term value: 220 mg/m³, 50 ppm
Sk; BMGV

78-93-3 butanone

WEL () Short-term value: 899 mg/m³, 300 ppm
Long-term value: 600 mg/m³, 200 ppm
Sk, BMGV

67-63-0 propan-2-ol

WEL () Short-term value: 1250 mg/m³, 500 ppm
Long-term value: 999 mg/m³, 400 ppm

106-97-8 butane

WEL () Short-term value: 1810 mg/m³, 750 ppm
Long-term value: 1450 mg/m³, 600 ppm
Carc (if more than 0.1% of buta-1.3-diene)

· **Ingredients with biological limit values:**

1330-20-7 xylene

BMGV () 650 mmol/mol creatinine
Medium: urine
Sampling time: post shift
Parameter: methyl hippuric acid

78-93-3 butanone

BMGV () 70 µmol/L
Medium: urine
Sampling time: post shift
Parameter: butan-2-one

· **Additional information:** The lists valid during the making were used as basis.

· 8.2 Exposure controls

· Personal protective equipment:

· General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.

· Respiratory protection:

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· Protection of hands:

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 5)



Protective gloves

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

9 Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Aerosol
Colour:	Colourless
Odour:	Characteristic
Odour threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Not applicable, as aerosol.

· **Flash point:** < 0 °C (< 32 °F)
Not applicable, as aerosol.

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 200 °C (392 °F)

· **Decomposition temperature:** Not determined.

· **Self-igniting:** Product is not selfigniting.

· **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

· **Explosion limits:**

Lower:	0.6 Vol %
Upper:	12.0 Vol %

· **Vapour pressure at 20 °C (68 °F):** 3500 hPa (2625 mm Hg)

· **Density at 20 °C (68 °F):** 0.727 g/cm³ (6.067 lbs/gal)

· **Relative density** Not determined.

· **Vapour density** Not determined.

· **Evaporation rate** Not applicable.

· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 6)

- **Partition coefficient (n-octanol/water):** Not determined.
- **Viscosity:**
 - Dynamic:** Not determined.
 - Kinematic:** Not determined.
- **Solvent content:**
 - Organic solvents:** 100.0 %
- **EU-VOC:** 727.0 g/l
- **EU-VOC in %:** 100.00 %
- **9.2 Other information** No further relevant information available.

10 Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**

· LD/LC50 values relevant for classification:

1330-20-7 xylene

Oral	LD50	4300 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
Inhalative	LC50 / 4 h	22.1 mg/m3 (rat)

78-93-3 butanone

Oral	LD50	2737 mg/kg (rat)
Dermal	LD50	6480 mg/kg (rabbit)
Inhalative	LC50 / 4 h	34 mg/m3 (rat)

67-63-0 propan-2-ol

Oral	LD50	5045 mg/kg (rat)
Dermal	LD50	12800 mg/kg (rabbit)
Inhalative	LC50 / 4 h	30 mg/m3 (rat)

64742-49-0 Naphtha (petroleum), hydrotreated light (< 0,1 % benzol CAS nr. 71-43-2)

Oral	LD50	>5840 mg/kg (rat)
Dermal	LD50	>2920 mg/kg (rabbit)
Inhalative	LC50 / 4 h	>193 mg/m3 (rat)
	LC50 / 4h	25.2 mg/l (rat)
	LC50 / 96 h	11.4 mg/l (fish)

106-97-8 butane

Inhalative	LC50 / 4 h	658000 mg/m3 (rat)
------------	------------	--------------------

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 7)

· **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:

Harmful

Irritant

12 Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

1330-20-7 xylene

EC50 / 48 h 7.4 mg/l (daphnia magna)

LC50 / 96 h 13.5 mg/l (fish)

67-63-0 propan-2-ol

EC50 / 48 h 13299 mg/l (daphnia magna)

LC50 / 96 h (dynamic) 4200 mg/l (fish)

64742-49-0 Naphtha (petroleum), hydrotreated light (< 0,1 % benzol CAS nr. 71-43-2)

EC50 / 48 h 3 mg/l (daphnia magna)

EC50 / 72 h 30-100 mg/l (algae)

LC50 / 96 h 93-117 mg/l (fish)

· **12.2 Persistence and degradability** No further relevant information available.

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **Ecotoxicological effects:**

· **Remark:** Harmful to fish

· **Additional ecological information:**

· **General notes:**

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

Harmful to aquatic organisms

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Other adverse effects** No further relevant information available.

13 Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **European waste catalogue**

20 01 13* solvents

15 01 04 metallic packaging

· **Uncleaned packaging:**

· **Recommendation:** Non contaminated packagings may be recycled.

GB

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 8)

14 Transport information

· 14.1 UN-Number	UN1950
· ADR, IMDG, IATA	
· 14.2 UN proper shipping name	1950 AEROSOLS
· ADR	AEROSOLS
· IMDG	AEROSOLS, flammable
· IATA	
· 14.3 Transport hazard class(es)	
· ADR	
	
· Class	2 5F Gases.
· Label	2.1
· IMDG, IATA	
	
· Class	2.1
· Label	2.1
· 14.4 Packing group	
· ADR, IMDG, IATA	Void
· 14.5 Environmental hazards:	
· Marine pollutant:	No
· 14.6 Special precautions for user	Warning: Gases.
· Danger code (Kemler):	-
· EMS Number:	F-D,S-U
· 14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR	
· Limited quantities (LQ)	1L
· Transport category	2
· Tunnel restriction code	D
· UN "Model Regulation":	UN1950, AEROSOLS, 2.1

15 Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
No further relevant information available.
- 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 28.03.2014

Version number 4

Revision: 28.03.2014

Trade name: MOTIP EGR CLEANER

(Contd. of page 9)

· Relevant phrases

- H220 Extremely flammable gas.
 H225 Highly flammable liquid and vapour.
 H226 Flammable liquid and vapour.
 H280 Contains gas under pressure; may explode if heated.
 H304 May be fatal if swallowed and enters airways.
 H312 Harmful in contact with skin.
 H315 Causes skin irritation.
 H319 Causes serious eye irritation.
 H332 Harmful if inhaled.
 H336 May cause drowsiness or dizziness.
 H411 Toxic to aquatic life with long lasting effects.
- R10 Flammable.
 R11 Highly flammable.
 R12 Extremely flammable.
 R20/21 Harmful by inhalation and in contact with skin.
 R36 Irritating to eyes.
 R38 Irritating to skin.
 R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
 R65 Harmful: may cause lung damage if swallowed.
 R66 Repeated exposure may cause skin dryness or cracking.
 R67 Vapours may cause drowsiness and dizziness.

· Department issuing MSDS: QHSE Department**· Contact: Mr. K. Smedeman****· Abbreviations and acronyms:**

- ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 GHS: Globally Harmonized System of Classification and Labelling of Chemicals
 EINECS: European Inventory of Existing Commercial Chemical Substances
 ELINCS: European List of Notified Chemical Substances
 CAS: Chemical Abstracts Service (division of the American Chemical Society)
 LC50: Lethal concentration, 50 percent
 LD50: Lethal dose, 50 percent
 Flam. Gas 1: Flammable gases, Hazard Category 1
 Flam. Aerosol 1: Flammable aerosols, Hazard Category 1
 Press. Gas: Gases under pressure: Compressed gas
 Flam. Liq. 2: Flammable liquids, Hazard Category 2
 Flam. Liq. 3: Flammable liquids, Hazard Category 3
 Acute Tox. 4: Acute toxicity, Hazard Category 4
 Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
 Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2
 STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3
 Asp. Tox. 1: Aspiration hazard, Hazard Category 1
 Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2
 Aquatic Chronic 3: Hazardous to the aquatic environment - Chronic Hazard, Category 3

· * Data compared to the previous version altered.

GB