



Assembly set for pressure vessels, fully threaded ISO 4017/4032 Stal (AD-W7) Ocynkowane na gorąco 5.6/5.2 do zbiorników ciśnieniowych M12X30

Numer artykułu	08762.120.030
Marka	-
UBB	500648358744
UNSPSC	31161620
Numer EAN	8717077245792
Opakowanie 100	Tylko pełne opakowanie

Parametry techniczne

Diameter	M12
Length	30 mm
Klasa	5.6/5.2
Gniazdo	Hexagon
Kształt łba	Łeb sześciokątny
Materiał	Stal (AD-W7)
Kierunek gwintu	Prawy
Obróbka powierzchni	Ocynkowane na gorąco
Gwint	Metryczny

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7,

Normy

ISO	4017/4032
-----	-----------

TRD106 and DIN
267-13 Manufacturers
included in VdTÜV-
Merkblatt 1253/4 are
entitled to replace a
certificate EN 10204
3.1 by marking the
fasteners with the
property class and
the manufacturer's
mark. This
recognition is equally
accepted by Lloyd's
Register Energy.do
zbiorników
ciśnieniowych

Specyfikacja techniczna

d-D	M12
k	7.5
L (mm)	30
m (maks.)	10.8
P	1.75
s	18

Rysunek techniczny

