FABORY



M12 S/25

Číslo položky	90252FIS
Značka	-
UBB	500616785662
UNSPSC	31161607
EAN	4006209902523
PKG. of 1	Len kompletné balenie

Technické parametre

Priemer	12 mm
Dĺžka	110 mm
Kľúčové vlastnosti	Functioning - The TAM is suitable for pre-positioned installation. - When applying the torque, the cone is pulled into the expansion sleeve and expands it against the drill hole wall. - For correct installation, it must be ensured that the pre-positioned anchor TA M can be supported on the attachment, or that the threaded rod is countered. - Determining the screw length l s : Screw length l s = Length of fixing + Thickness of fixture t fix + Thickness of washer.
ETA-Certifikát	Yes
Info	do= Nominal diameter of drill bit.dd= Embedment depth.df= Anchor diameter.fs= Head

Normy

diameter.Ws= Setting tool diameter.hef= Effective anchorage depth.tfix= Grip range.kN = Allowable load in kN.

Technické špecifikácie

Technický nákres

