



Sprężyny talerzowe do zastosowań krytycznych, typ A (powiększone) EN 16983 A Stal acc. to EN 16983 Fosfatowane 140X72,0X8,0MM

Numer artykułu	36300.976.080
----------------	---------------

Marka	-
-------	---

UBB	500644901752
-----	--------------

UNSPSC	31161811
--------	----------

Numer EAN	8717077039575
-----------	---------------

Opakowanie 1	Tylko pełne opakowanie
--------------	------------------------

Parametry techniczne

Diameter	72 mm
d _e	140
d _i	72
Materiał	Stal
Materiał techniczny	acc. to EN 16983
Średnica zewnętrzna	140
Obróbka powierzchni	Fosfatowane
Typ nr.	A

Normy

DIN	2093-A
EN	16983-A

Info

Warning: electroplating of these products may cause hydrogen embrittlement. F = spring load in Newton at a deflection $s \approx 0,75 h_0$ ($h_0 = l_0 - t$). The values specified for t are nominal values. In the case of springs with $6 < t \leq 14$ the desired spring load F is to be obtained

by reducing the thickness of single disc springs t to the values between brackets. Refer to EN 16984 for calculation of disc springs. Extensive technical data available on request.

Specyfikacja techniczna

d_i (H12)	72
D (mm)	72
F	85251
l_0	11.2
t	8
Grubość	8

Rysunek techniczny

