

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : MOLYKOTE(R) 33 EXTREME LOW TEMP. BEARING GREASE, MEDIUM

Product code : 000000000001889788, 000000000001889788

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-stance/Mixture : Lubricants and lubricant additives

1.3 Details of the supplier of the safety data sheet

Company : Dow Corning Europe S.A.
rue Jules Bordet - Parc Industriel - Zone C
B-7180 Seneffe

Telephone : English Tel: +49 611237507
Deutsch Tel: +49 611237500
Français Tel: +32 64511149
Italiano Tel: +32 64511170
Español Tel: +32 64511163

E-mail address of person responsible for the SDS : sdseu@dowcorning.com

1.4 Emergency telephone number

Dow Corning (Barry U.K. 24h) Tél: +44 1446732350
Dow Corning (Wiesbaden 24h) Tél: +49 61122158
Dow Corning (Seneffe 24h) Tel: +32 64 888240

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.3 Other hazards

None known.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Chemical nature : Silicone grease

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version 1.5	Revision Date: 30.10.2015	SDS Number: 641093-00006	Date of last issue: 24.09.2015 Date of first issue: 16.10.2014
----------------	------------------------------	-----------------------------	---

Hazardous components

Remarks : No hazardous ingredients

SECTION 4: First aid measures

4.1 Description of first aid measures

Protection of first-aiders	: No special precautions are necessary for first aid responders.
If inhaled	: If inhaled, remove to fresh air. Get medical attention if symptoms occur.
In case of skin contact	: Wash with water and soap as a precaution. Get medical attention if symptoms occur.
In case of eye contact	: Flush eyes with water as a precaution. Get medical attention if irritation develops and persists.
If swallowed	: If swallowed, DO NOT induce vomiting. Get medical attention if symptoms occur. Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

None known.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media	: Water spray Alcohol-resistant foam Carbon dioxide (CO ₂) Dry chemical
Unsuitable extinguishing media	: None known.

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting	: Exposure to combustion products may be a hazard to health.
Hazardous combustion products	: Carbon oxides Silicon oxides Formaldehyde Metal oxides

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue:
1.5	30.10.2015	641093-00006	24.09.2015
			Date of first issue: 16.10.2014

5.3 Advice for firefighters

- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- Personal precautions : Follow safe handling advice and personal protective equipment recommendations.

6.2 Environmental precautions

- Environmental precautions : Discharge into the environment must be avoided.
Prevent further leakage or spillage if safe to do so.
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and material for containment and cleaning up

- Methods for cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice.
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store in accordance with the particular national regulations.

Advice on common storage : Do not store with the following product types:
Strong oxidizing agents

7.3 Specific end use(s)

Specific use(s) : These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value
Lithium stearate	Workers	Inhalation	Long-term systemic effects	3 mg/m3
	Workers	Inhalation	Acute systemic effects	6 mg/m3
	Workers	Skin contact	Long-term systemic effects	41 mg/kg bw/day
	Workers	Skin contact	Acute systemic effects	41 mg/kg bw/day
	Workers	Skin contact	Long-term local effects	0.172 mg/cm2
	Consumers	Skin contact	Long-term systemic effects	41 mg/kg bw/day
	Consumers	Skin contact	Acute systemic effects	41 mg/kg bw/day
	Consumers	Skin contact	Long-term local effects	0.086 mg/cm2

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version 1.5 Revision Date: 30.10.2015 SDS Number: 641093-00006 Date of last issue: 24.09.2015
Date of first issue: 16.10.2014

	Consumers	Ingestion	Long-term systemic effects	41 mg/kg bw/day
	Consumers	Ingestion	Acute systemic effects	41 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
Lithium stearate	Fresh water	0.1 mg/l
	Marine water	0.01 mg/l
	Intermittent use/release	1 mg/l

8.2 Exposure controls

Engineering measures

Processing may form hazardous compounds (see section 10).
Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye protection : Wear the following personal protective equipment:
Safety glasses

Hand protection
Remarks : Wash hands before breaks and at the end of workday.

Skin and body protection : Skin should be washed after contact.

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Filter type : Particulates type (P)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : Grease

Colour : white

Odour : slight

Odour Threshold : No data available

pH : Not applicable

Melting point/freezing point : No data available

Initial boiling point and boiling range : Not applicable

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version 1.5	Revision Date: 30.10.2015	SDS Number: 641093-00006	Date of last issue: 24.09.2015 Date of first issue: 16.10.2014
----------------	------------------------------	-----------------------------	---

Flash point	: > 101.1 °C Method: closed cup
Evaporation rate	: Not applicable
Flammability (solid, gas)	: Not classified as a flammability hazard
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: Not applicable
Relative vapour density	: No data available
Relative density	: 1.1
Solubility(ies)	
Water solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity	
Viscosity, dynamic	: Not applicable
Explosive properties	: Not explosive
Oxidizing properties	: The substance or mixture is not classified as oxidizing.

9.2 Other information

Molecular weight	: No data available
------------------	---------------------

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions	: Use at elevated temperatures may form highly hazardous compounds. Can react with strong oxidizing agents. Hazardous decomposition products will be formed at elevated
---------------------	---

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

temperatures.

10.4 Conditions to avoid

Conditions to avoid : None known.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

10.6 Hazardous decomposition products

Thermal decomposition : Benzene
Formaldehyde

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Information on likely routes of exposure : Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

Product:

Assessment: Does not cause skin sensitisation.

Test Type: Maximisation Test

Species: Guinea pig

Remarks: Based on test data

Germ cell mutagenicity

Not classified based on available information.

Product:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: Based on test data

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version 1.5	Revision Date: 30.10.2015	SDS Number: 641093-00006	Date of last issue: 24.09.2015 Date of first issue: 16.10.2014
----------------	------------------------------	-----------------------------	---

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Not relevant

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- | | |
|------------------------|---|
| Product | : Dispose of in accordance with local regulations.
According to the European Waste Catalogue, Waste Codes are not product specific, but application specific.
Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities. |
| Contaminated packaging | : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product. |

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

The components of this product are reported in the following inventories:

KECI : All ingredients listed, exempt or notified.

TCSI : All ingredients listed or exempt.

REACH : All ingredients (pre-)registered or exempt.

TSCA : All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical Substances.

AICS : All ingredients listed or exempt.

IECSC : All ingredients listed or exempt.

ENCS/ISHL : All components are listed on ENCS/ISHL or exempted from

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

inventory listing.

PICCS	: All ingredients listed or exempt.
DSL	: All chemical substances in this product comply with the CEPA 1999 and NSNR and are on or exempt from listing on the Canadian Domestic Substances List (DSL).
NZIoC	: All ingredients listed or exempt.

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to compile the Safety Data	: Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agen-
---	---

**MOLYKOTE(R) 33 EXTREME LOW TEMP.
BEARING GREASE, MEDIUM**

Version	Revision Date:	SDS Number:	Date of last issue: 24.09.2015
1.5	30.10.2015	641093-00006	Date of first issue: 16.10.2014

Sheet cy, <http://echa.europa.eu/>

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

GB / EN