

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

### 1 Identification of the substance/mixture and of the company/undertaking

- **Product identifier**
- **Trade name:** MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black
- **Article number:** 04003 / 04007 / 04008 / 04010 / 04018 / 04019 02000 (Silver 150 ml)
- **Relevant identified uses of the substance or mixture and uses advised against**
- **Application of the substance / the preparation** Paint
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolfraamweg 2  
NL-8471 XC Wolvega  
The Netherlands  
Tel: +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail info@nl.motipdupli.com
- **Further information obtainable from:** QHSE Department
- **Emergency telephone number:** Tel: +31 (0)561 694400 (08.00 / 17.00)

### 2 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Aerosol 1 H222 Extremely flammable aerosol.



GHS05 corrosion

Eye Dam. 1 H318 Causes serious eye damage.



GHS07

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xi; Irritant

R36: Irritating to eyes.



F+; Extremely flammable

R12: Extremely flammable.

R66-67: Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness.

- **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

At long or repeated contact with skin it may cause dermatitis due to the degreasing effect of the solvent.

Warning! Pressurized container.

Has a narcotizing effect.

(Contd. on page 2)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

**Trade name: MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 1)

**Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

**Label elements**
**Labelling according to EU guidelines:**

The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

**Code letter and hazard designation of product:**


Xi Irritant

F+ Extremely flammable

**Risk phrases:**

- 12 Extremely flammable.
- 36 Irritating to eyes.
- 66 Repeated exposure may cause skin dryness or cracking.
- 67 Vapours may cause drowsiness and dizziness.

**Safety phrases:**

- 2 Keep out of the reach of children.
- 16 Keep away from sources of ignition - No smoking.
- 23 Do not breathe aerosol.
- 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- 29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.
- 46 If swallowed, seek medical advice immediately and show this container or label.
- 51 Use only in well-ventilated areas.

**Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

**Classification in accordance with Directive 75/324/EEC: Extremely flammable**
**Other hazards**
**Results of PBT and vPvB assessment**

**PBT:** Not applicable.

**vPvB:** Not applicable.

### 3 Composition/information on ingredients

**Chemical characterization: Mixtures**

**Description:** Mixture of substances listed below with nonhazardous additions.

**Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2	acetone Xi R36 F R11 R66-67 <hr style="border-top: 1px dashed black;"/> Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	25-50%
-----------------------------------	---	--------

(Contd. on page 3)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

Trade name: **MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 2)

CAS: 123-86-4 EINECS: 204-658-1	n-butyl acetate R10-66-67 Flam. Liq. 3, H226 STOT SE 3, H336	10-12.5%
CAS: 74-98-6 EINECS: 200-827-9	propane F+ R12 Flam. Gas 1, H220 Press. Gas, H280	10-12.5%
CAS: 106-97-8 EINECS: 203-448-7	butane F+ R12 Flam. Gas 1, H220 Press. Gas, H280	5-10%
CAS: 75-28-5 EINECS: 200-857-2	isobutane F+ R12 Flam. Gas 1, H220 Press. Gas, H280	5-10%
CAS: 78-93-3 EINECS: 201-159-0	butanone Xi R36 F R11 R66-67 Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	5-10%
CAS: 108-65-6 EINECS: 203-603-9	2-methoxy-1-methylethyl acetate R10 Flam. Liq. 3, H226	5-10%
CAS: 71-36-3 EINECS: 200-751-6	butan-1-ol Xn R22 Xi R37/38-41 R10-67 Flam. Liq. 3, H226 Eye Dam. 1, H318 Acute Tox. 4, H302; STOT SE 3, H335+H336 Skin Irrit. 2, H315	2.5-5%
CAS: 9004-70-0	Nitrocellulose (nitrogen content <12.6%) F R11 Flam. Sol. 1, H228	2.5-5%
CAS: 67-63-0 EINECS: 200-661-7	propan-2-ol Xi R36 F R11 R67 Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	1-2.5%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

#### 4 First aid measures

· **Description of first aid measures**

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.

· **After skin contact:** Generally the product does not irritate the skin.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.

· **Information for doctor:**

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

(Contd. on page 4)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

**Trade name: MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 3)

- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### 5 Firefighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**  
Ensure adequate ventilation  
Keep away from ignition sources.
- **Environmental precautions:**  
Do not allow product to reach sewage system or any water course.  
Inform respective authorities in case of seepage into water course or sewage system.  
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### 7 Handling and storage

- **Handling:**
- **Precautions for safe handling**  
No special measures required.  
Ensure good ventilation/exhaustion at the workplace.  
Open and handle receptacle with care.
- **Information about fire - and explosion protection:**  
Do not spray onto a naked flame or any incandescent material.  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.  
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Store in a cool location.  
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**  
Keep container tightly sealed.  
Protect from heat and direct sunlight.
- **Specific end use(s)** No further relevant information available.

GB

(Contd. on page 5)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

Trade name: **MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 4)

### 8 Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

#### 67-64-1 acetone

WEL Short-term value: 3620 mg/m<sup>3</sup>, 1500 ppm  
Long-term value: 1210 mg/m<sup>3</sup>, 500 ppm

#### 123-86-4 n-butyl acetate

WEL Short-term value: 966 mg/m<sup>3</sup>, 200 ppm  
Long-term value: 724 mg/m<sup>3</sup>, 150 ppm

#### 106-97-8 butane

WEL Short-term value: 1810 mg/m<sup>3</sup>, 750 ppm  
Long-term value: 1450 mg/m<sup>3</sup>, 600 ppm  
Carc (if more than 0.1% of buta-1.3-diene)

#### 78-93-3 butanone

WEL Short-term value: 899 mg/m<sup>3</sup>, 300 ppm  
Long-term value: 600 mg/m<sup>3</sup>, 200 ppm  
Sk

#### 108-65-6 2-methoxy-1-methylethyl acetate

WEL Short-term value: 548 mg/m<sup>3</sup>, 100 ppm  
Long-term value: 274 mg/m<sup>3</sup>, 50 ppm  
Sk

#### 71-36-3 butan-1-ol

WEL Short-term value: 154 mg/m<sup>3</sup>, 50 ppm  
Sk

#### 67-63-0 propan-2-ol

WEL Short-term value: 1250 mg/m<sup>3</sup>, 500 ppm  
Long-term value: 999 mg/m<sup>3</sup>, 400 ppm

· **Additional information:** The lists valid during the making were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

· **Respiratory protection:** Not required.

· **Protection of hands:** Not required.

· **Material of gloves:** Not required.

· **Penetration time of glove material:** Not required.

· **Eye protection:**



Tightly sealed goggles

GB

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

Trade name: **MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 5)

## 9 Physical and chemical properties

· <b>Information on basic physical and chemical properties</b>	
· <b>General Information</b>	
· <b>Appearance:</b>	
Form:	Aerosol
Colour:	According to product specification
· <b>Odour:</b>	Characteristic
· <b>Odour threshold:</b>	Not determined.
· <b>pH-value:</b>	Not determined.
· <b>Change in condition</b>	
Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Not applicable, as aerosol.
· <b>Flash point:</b>	< 0°C (< 32°F) Not applicable, as aerosol.
· <b>Ignition temperature:</b>	315°C (599°F)
· <b>Decomposition temperature:</b>	Not determined.
· <b>Self-igniting:</b>	Product is not selfigniting.
· <b>Danger of explosion:</b>	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· <b>Explosion limits:</b>	
Lower:	1.2 Vol %
Upper:	13.0 Vol %
· <b>Vapour pressure at 20°C (68°F):</b>	3500 hPa (2625 mm Hg)
· <b>Density at 20°C (68°F):</b>	0.766 g/cm <sup>3</sup> (6.392 lbs/gal)
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not applicable.
· <b>Solubility in / Miscibility with water:</b>	Not miscible or difficult to mix.
· <b>Segregation coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
Dynamic:	Not determined.
Kinematic:	Not determined.
· <b>Solvent content:</b>	
Organic solvents:	87.9 %
· <b>EU-VOC:</b>	673.5 g/l
· <b>EU-VOC in %:</b>	87.93 %
· <b>Solids content:</b>	3.0 %
· <b>Other information</b>	No further relevant information available.

## 10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

Trade name: **MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 6)

· **Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

· **Information on toxicological effects**· **Acute toxicity:**· **LD/LC50 values relevant for classification:**

### 67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
Dermal	LD50	20000 mg/kg (rabbit)
	LC50 / 4 h	39 mg/m <sup>3</sup> (rat)

### 123-86-4 n-butyl acetate

Oral	LD50	10770 mg/kg (rat)
Dermal	LD50	>17600 mg/kg (rabbit)
	LC50 / 4 h	>21.0 mg/m <sup>3</sup> (rat)

### 106-97-8 butane

	LC50 / 4 h	658 mg/m <sup>3</sup> (rat)
--	------------	-----------------------------

### 78-93-3 butanone

Oral	LD50	2737 mg/kg (rat)
Dermal	LD50	6480 mg/kg (rabbit)
	LC50 / 4 h	34 mg/m <sup>3</sup> (rat)

### 108-65-6 2-methoxy-1-methylethyl acetate

Oral	LD50	8532 mg/kg (rat)
Dermal	LD50	>5000 mg/kg (rabbit)
	LC50 / 4 h	35.7 mg/m <sup>3</sup> (rat)

### 71-36-3 butan-1-ol

Oral	LD50	4400 mg/kg (rat)
Dermal	LD50	4200 mg/kg (rabbit)
	LC50 / 4 h	25 mg/m <sup>3</sup> (rat)

### 67-63-0 propan-2-ol

Oral	LD50	5045 mg/kg (rat)
Dermal	LD50	12800 mg/kg (rabbit)
	LC50 / 4 h	30 mg/m <sup>3</sup> (rat)

· **Primary irritant effect:**· **on the skin:** No irritant effect.· **on the eye:** Irritating effect.· **Sensitization:** No sensitizing effects known.· **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:

Irritant

## 12 Ecological information

· **Toxicity**· **Aquatic toxicity:**

### 67-64-1 acetone

EC50 / 48 h	39 mg/l (daphnia magna)
-------------	-------------------------

(Contd. on page 8)



# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

**Trade name: MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 7)

LC50 / 48 h	2262 mg/l (daphnia magna)
LC50 / 96 h (static)	5540 mg/l (fish)
<b>123-86-4 n-butyl acetate</b>	
EC50 / 96 h	320 mg/l (algae)
LC50 / 24 h	205 mg/l (daphnia magna)
<b>108-65-6 2-methoxy-1-methylethyl acetate</b>	
EC50	408 mg/l (daphnia magna)
<b>71-36-3 butan-1-ol</b>	
EC50 / 48 h	1983 mg/l (daphnia magna)
EC50 / 72 h	8500 mg/l (algae)
<b>67-63-0 propan-2-ol</b>	
EC50 / 48 h	13299 mg/l (daphnia magna)
LC50 / 96 h (dynamic)	4200 mg/l (fish)

- **Persistence and degradability** No further relevant information available.
- **Behaviour in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
 Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
 Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

### 13 Disposal considerations

- **Waste treatment methods**
  - **Recommendation**  
 Must not be disposed together with household garbage. Do not allow product to reach sewage system.
  - **European waste catalogue**
- |           |   |
|-----------|---|
| 08 01 11* | waste paint and varnish containing organic solvents or other dangerous substances |
| 15 01 04  | metallic packaging  |
- **Uncleaned packaging:**
  - **Recommendation:** Disposal must be made according to official regulations.

### 14 Transport information

- **Land transport ADR/RID (cross-border)**



- **ADR/RID class:** 2 5F Gases.
- **Danger code (Kemler):** -
- **UN-Number:** 1950
- **Packaging group:** -
- **Hazard label** 2.1

(Contd. on page 9)



# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

**Trade name: MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 8)

- **UN proper shipping name:** 1950 AEROSOLS
- **Limited quantities (LQ)** LQ2
- **Transport category** 2
- **Tunnel restriction code** D

**· Maritime transport IMDG:**


- **IMDG Class:** 2.1
- **UN Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **EMS Number:** F-D,S-U
- **Marine pollutant:** No
- **Proper shipping name:** AEROSOLS

**· Air transport ICAO-TI and IATA-DGR:**


- **ICAO/IATA Class:** 2.1
- **UN/ID Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **Proper shipping name:** AEROSOLS, flammable

- **UN "Model Regulation":** UN1950, AEROSOLS, 2.1
- **Special precautions for user** Warning: Gases.
- **Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code** Not applicable.

### 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Labelling according to EU guidelines:**  
The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

**· Code letter and hazard designation of product:**


Xi Irritant  
F+ Extremely flammable

- **Risk phrases:**
  - 12 Extremely flammable.
  - 36 Irritating to eyes.
  - 66 Repeated exposure may cause skin dryness or cracking.
  - 67 Vapours may cause drowsiness and dizziness.

- **Safety phrases:**
  - 2 Keep out of the reach of children.
  - 16 Keep away from sources of ignition - No smoking.
  - 23 Do not breathe aerosol.
  - 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

(Contd. on page 10)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 23.03.2011

Version number 60

Revision: 23.03.2011

**Trade name: MOTIP WHEEL SPRAY White / Silver / Gold / Steel Wheel / Black**

(Contd. of page 9)

29/56 Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point.

46 If swallowed, seek medical advice immediately and show this container or label.

51 Use only in well-ventilated areas.

· **Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

· **Classification in accordance with Directive 75/324/EEC:** Extremely flammable

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H228 Flammable solid.

H280 Contains gas under pressure; may explode if heated.

H302 Harmful if swallowed.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

H336 May cause drowsiness or dizziness.

R10 Flammable.

R11 Highly flammable.

R12 Extremely flammable.

R22 Harmful if swallowed.

R36 Irritating to eyes.

R37/38 Irritating to respiratory system and skin.

R41 Risk of serious damage to eyes.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

· **Department issuing MSDS:** QHSE Department

· **Contact:**

Mrs. D. Kleistra

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

· **\* Data compared to the previous version altered.**

GB