



## Machine screw pan head slot UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) 1/4-20X1.

Article number	U51120.025.0100
Brand	-
UBB	500624999057
UNSPSC	31161504
EAN	8717077795839
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	1/4 Inch
Length	1 Inch
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	20

Info  
Screws with diameter  $\leq$  No.5 and length  $\leq$  1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length  $\leq$  2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

### Standards

ASME B18.6.3

### Technical Specification

A (max.)	0.492
H (max.)	0.144

### Technical Drawing

J (max.)	0.075
T (max.)	0.087

**FABORY**

