



Revision Number: 006.0

Issue date: 09/12/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE SI 5699 GY CR300ML EGFD	IDH number:	2061026
Product type:	Silicone	Item number:	SOP
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: +1 (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Avoid breathing dust or fumes. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Wash contaminated clothing before reuse.
Storage:	Not prescribed
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Calcium carbonate	471-34-1	10 - 30

Butan-2-one O,O',O''-(vinylsilyldiyl)trioxime	2224-33-1	5 - 10
Silica, amorphous, treated	68909-20-6	1 - 5
Butan-2-one O,O',O'',O'''-silanetetrayltetraoxime	34206-40-1	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If symptoms develop and persist, get medical attention.
Skin contact:	Wipe off paste with paper towel or cloth. Wash with soap and water. If skin irritation persists, call a physician.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. In case of adverse health effects seek medical advice.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self contained breathing apparatus. Prevent inhalation of fumes and gases.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of silicon. Formaldehyde. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow material to contaminate ground water system.
Clean-up methods:	Scrape up as much material as possible. Maintain good ventilation for large spills. Place scrap material in a well ventilated area and allow to cure to rubber.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not handle contact lenses until all sealant has been removed from hands. Residual sealant may transfer to lenses and cause eye irritation.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Calcium carbonate	10 mg/m3 TWA Total dust.	5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust.	None	None
Butan-2-one O,O',O''-(vinylsilyldyne)trioxime	None	None	None	None
Silica, amorphous, treated	10 mg/m3 TWA Inhalable dust.	6 mg/m3 TWA	None	None
Butan-2-one O,O',O'',O'''-silanetetrayltetraoxime	None	None	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.

Eye/face protection:

Safety goggles or safety glasses with side shields. Safety showers and eye wash stations should be available.

Skin protection:

Use impermeable gloves and protective clothing as necessary to prevent skin contact. Nitrile gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste
Color:	Gray
Odor:	Mild
Odor threshold:	Not available.
pH:	Not applicable
pH:	Not applicable
Vapor pressure:	< 5 mm hg
Boiling point/range:	> 200 °C (> 392°F)
Melting point/ range:	Not available.
Specific gravity:	1.5 at 20 °C (68°F)
Vapor density:	Heavier than air.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not applicable
Flammable/Explosive limits - upper:	Not applicable
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Polymerises in presence of water.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	3.31 %; 49.65 g/l
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of silicon. Oxides of carbon. Methyl ethyl ketoxime formed during cure. Formaldehyde. Irritating fumes.
Incompatible materials:	Acids and bases. Oxidizing agents. Polymerizes on contact with water.
Reactivity:	Not available.
Conditions to avoid:	Excessive heat. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation:	May cause respiratory tract irritation. When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit.
Skin contact:	May cause allergic skin reaction. May cause skin irritation.
Eye contact:	Causes serious eye irritation.
Ingestion:	Not expected under normal conditions of use. May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Calcium carbonate	Oral LD50 (Rat) = 6,450 mg/kg Oral LD50 (Mouse) = 6,450 mg/kg	Nuisance dust
Butan-2-one O,O',O"- (vinylsilylidyne)trioxime	None	Irritant, Allergen
Silica, amorphous, treated	None	No Target Organs
Butan-2-one O,O',O",O'''- silanetetrayltetraoxime	None	Irritant, Allergen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Calcium carbonate	No	No	No
Butan-2-one O,O',O"- (vinylsilylidyne)trioxime	No	No	No
Silica, amorphous, treated	No	No	No
Butan-2-one O,O',O",O'''- silanetetrayltetraoxime	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal. Cured rubber can be incinerated or landfilled following EPA and local regulations.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None
Exceptions: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.

CERCLA/SARA Section 311/312: Immediate Health, Delayed Health

CERCLA/SARA Section 313: None above reporting de minimis.

California Proposition 65: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 2, 3, 8

Prepared by: Product Safety and Regulatory Affairs

Issue date: 09/12/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.