



## Structural assembly set, fully threaded ISO metric thread EN 15048 Steel Hot dip galvanized 8.8/8 M12X60

Article number	01415.120.060
Brand	-
UBB	500574466891
UNSPSC	31161620
EAN	8715494289535
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M12
Length	60 mm
Class	8.8/8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

#### Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

### Standards

EN	15048
ISO	4017/4032

bolting according to EN 15048-1 are compliant with the CPR. Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are packaged together in single sealed boxes. A Declaration of Performance (DoP) is available. ISO metric

## Technical Specification

d-D	M12
k	7.5
L (mm)	60
m (max.)	10.8
P	1.75
s	18

## Technical Drawing

