



**Conical sheet metal bit drill.
range 16-30.5 mm HSS-Co
overall length 76 mm no.**

Article number	1N680925
Brand	-
UBB	500581131306
UNSPSC	27112812
EAN	4015448555391
PKG. of 1	Full Box Only

Technical Parameters

Shaft diameter	9
Number of cutting blades	2
Unit of measurement	mm
Max. drill diameter	30.5
Min. drill diameter	16
Cutting material	HSS-E

Standards